


## Cable Runway Corner Bracket Kit for 12 in. and 18 in. Ladder Runway, Straight - Hardware Included

MODEL NUMBER: **SRLCRNSPPT**



Provides structural support and creates a radius for connecting an L-, T- or X-shaped intersection in your custom-designed cable runway.

### Features

**Cable Ladder Corner Bracket Helps You Create Custom Data-Center Runway Schemes** This exclusive SmartRack® Cable Runway Corner Bracket kit creates a secure connection point between two intersecting sections of cable ladder in your server room or data center. This allows you to create a radius for L-, T- or X-shaped intersections of cable runway and shape the direction of cabling to your liking. The corner support adds a radius that further strengthens and supports the runway, allowing for more voluminous and comprehensive runs. Mounting and installation hardware is included. The corner clamp plates are easy to install and fit solid and tubular steel runway measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). The SRLCRNSPPT is designed for Tripp Lite's SRCABLELADDER, SRCABLELADDER18 and other compatible 12-inch (305-millimeter) and 18-inch (457-millimeter) straight ladder sections.

### Highlights

- Securely connects cable management ladders outside an enclosure or open frame rack
- Allows you more flexibility in routing custom cable management schemes
- Compatible with both 12 in. (305 mm) and 18 in. (457 mm) straight ladder sections
- Fits solid and tubular steel runway measuring 1.5 x 0.375 in. (38 x 9.5 mm)
- Includes all necessary mounting and installation hardware for immediate use

### Applications

- Organize a ladder runway system with intersecting sections outside your data center's rack enclosure or open frame rack

### System Requirements

- Compatible with 12 in. (305 mm) and 18 in. (457 mm) straight ladder sections, including Tripp Lite SRCABLELADDER and SRCABLELADDER18

### Package Includes

- Corner bracket
- (4) Clamps
- (4) M6 bolts
- (4) M6 split-lock washers
- (4) M6 nuts
- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332214607
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	8.89 x 43.94 x 43.94
Shipping Dimensions (hwd / in.)	3.50 x 17.30 x 17.30
Shipping Weight (kg)	1.12
Shipping Weight (lbs.)	2.48
Unit Dimensions (hwd / cm)	38.99 x 38.99 x 3.81
Unit Dimensions (hwd / in.)	15.350 x 15.350 x 1.500
Unit Weight (kg)	1.03
Unit Weight (lbs.)	2.260
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[SRLCRNSPPT](#)