

USB-C Cable (M/M) - USB 2.0, 5A Rating, USB-IF Certified, Thunderbolt 3 Compatible, 3 m

MODEL NUMBER: U040-C3M-C-5A



Provides up to 20V 5A (100W) for powering and charging your MacBook Pro or other mobile device through a USB-C charger or power bank.

Features

USB-C to USB-C Cable Connects 2 USB-C Devices, Including MacBooks and Smartphones This three-meter USB Type-C to Type-C cable allows you to connect one USB-C device to another. For instance, a laptop to a docking station, your smartphone to a wall charger, or a hard drive or flash drive to a computer or tablet. The USB-C to C cable is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks.

PD Charging Cable Produces up to 100W for Rapid Syncing and Charging The Power Delivery cable provides power output up to 5 amps (100 watts), which is sufficient for fast-charging, syncing and powering most large-capacity devices, including the MacBook Pro. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB Type-C to USB Type-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connectors Attach in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line Performance This cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U040-C3M-C-5A meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

Highlights

- Certified by USB-IF to ensure highest-grade construction and performance
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Power Delivery cable provides 5A (100W) for fast-charging large-capacity devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-C wall charger up to 3 m away
- Transfer data between an external hard drive or flash drive and your laptop or computer
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

System Requirements

- Devices with USB-C or Thunderbolt 3 ports

Package Includes

- U040-C3M-C-5A USB-C to USB-C Cable, USB-IF, M/M, 3 m

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332241313
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	4.5MM
Cable Jacket Rating	VW-1
Cable Length (ft.)	9.8
Cable Length (m)	3
Cable Length (in.)	118
Material of Construction	PVC
Cable Length (cm)	300
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14 TO 140 F (-10 TO 60 C)
Storage Temperature Range	-4 TO 185 F (-20 TO 85 C)
Relative Humidity	10% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH, USB-IF
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U040-C3M-C-5A](#)