

## USB-C to SATA Quick Dock - USB 3.1 Gen 2 (10 Gbps), 2.5/3.5 in. HDD/SDD, Thunderbolt 3 Compatible

MODEL NUMBER: **U439-001-CG2**



USB-C to SATA dock connects a SATA hard drive to your computer, laptop, MacBook, Ultrabook or Chromebook's USB-C or Thunderbolt 3 port.

### Features

**USB-C to SATA Adapter Connects a SATA Drive to Your Device's USB-C or Thunderbolt 3 Port** This single-drive USB 3.1 Type-C to SATA quick dock allows you to quickly and easily add extra storage space to your computer, tablet, laptop, notebook, MacBook, Ultrabook or Chromebook. The plug-and-play unit connects to your device's USB Type-C or Thunderbolt 3 port using the included USB 3.1 Gen 2 cable. Just insert a 2.5- or 3.5-inch SATA drive into the top slot, and activate the on/off switch. An LED indicates a link with the device's USB port.

**Complies with USB 3.1 Gen 2 Standards for Ultra-Fast File Transfers** This USB Type-C to SATA adapter supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps. It is backward compatible with previous USB 3.0 and USB 2.0 generations, so you can use it with older USB devices and cables. It also reads data up to 70 percent faster and writes up to 40 percent faster when connected to a UASP-enabled host controller.

**Works with Most SATA Drives** The dock accepts 2.5-inch and 3.5-inch SATA I, II and III hard disc drives (HDDs) and solid state drives (SSDs) up to 10 TB (and higher-capacity drives when they become available). It also works with all major operating systems, including Windows, Mac and Linux.

### Highlights

- Ideal for system builders and IT pros who need quick access to drives for imaging
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps for ultra-fast file transfers
- Compatible with all 2.5 and 3.5 in. SATA I, II and III HDDs and SSDs up to 10 TB
- Works with all major operating systems, including Windows, Mac and Linux
- Plug-and-play operation with no software or drivers required

### Applications

- Add external storage to your PC or notebook computer
- Quickly archive backup data from your computer to an external drive
- Transfer data from one computer to another via SATA drive
- Gain fast access to SATA drives for imaging purposes

### System Requirements

- Computer with USB-C or Thunderbolt 3 port (USB 3.1 Gen 2 port required to achieve maximum speeds)
- 2.5 in. or 3.5 in. SATA HDD or SSD
- Any major operating system that complies with USB standards

### Package Includes

- U439-001-CG2 USB 3.1 Gen 2



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

#### USB-C to SATA Hard-Drive

#### Quick Dock

- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 12V 2A)
- USB 3.1 Gen 2 (10 Gbps) USB-C cable (M/M), 3 ft.
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332230973
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A, 4.9 ft.
Technology	USB 3.1 (Gen 1); SATA/eSATA; USB
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply Certifications	FCC; UL; cUL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power and Data)
PHYSICAL	
Color	Black
Material of Construction	Plastic



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Dimensions (hwd / in.)	3.15 x 6.69 x 5.12
Shipping Weight (kg)	0.25
Unit Dimensions (hwd / cm)	5.8 x 13.0 x 7.6
Unit Dimensions (hwd / in.)	2.3 x 5.1 x 3.0
Unit Packaging Type	Box
Unit Weight (kg)	0.50
Unit Weight (lbs.)	1.1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 148 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	7-PIN SATA (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
Driver Required	No
UASP Support	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U439-001-CG2](#)