

Dual-Port USB Car Charger for Tablets and Cell Phones with Quick Charge 2.0 Technology

MODEL NUMBER: **U280-C02-S-M6**



Built-in USB Micro-B cable with Quick Charge 2.0 and auto-sensing USB-A port allow you to charge 2 mobile devices, such as a tablet and cell phone, in your vehicle at the same time. Quick Charge 2.0 delivers up to 75% faster charging vs. conventional USB charging.

Description

The U280-C02-S-M6 Dual USB Car Charger lets you quickly and safely charge two USB-powered mobile devices in your vehicle at the same time. You and your passenger can connect your cell phones simultaneously to ensure full charges when you reach your destination.

Also ideal for tablets, MP3 players and other USB devices, the U280-C02-S-M6 features a built-in six-foot USB Micro-B cable with Quick Charge 2.0 technology for rapid charging of compliant devices. Available outputs include 5V 2A, 9V 1.67A and 12V 1.25A. The cable's auto-sensing technology allows it to also charge devices without Quick Charge capability at a maximum power output of 5V 2.4A. The specially coiled cable takes up much less space than a regular six-foot cable.

The U280-C02-S-M6's USB port also features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers. It's also compatible with both Apple and Android, as well as other platforms.

This ultra-compact charger works with any standard 12V DC vehicle power outlet. A front-facing LED indicates successful charging.

Features

Charge 2 Mobile Devices in Your Vehicle at the Same Time

- Ideal for cell phones, tablets, e-readers and MP3 players
- Auto-sensing USB port detects connected device and adjusts to proper power level up to 5V 2.4A
- Compatible with Apple, Android and other platforms

Highlights

- Quick Charge 2.0 Class A 5/9/12V technology
- USB Micro-B cable with Quick Charge provides optimal charging for compatible devices
- Ideal for cell phones, tablets, e-readers and MP3 players
- Auto-sensing USB-A port provides power output up to 5V 2.4A
- Works with any standard 12V DC vehicle power outlet
- Compatible with Apple, Android and other platforms

Package Includes

- U280-C02-S-M6 Dual USB Car Charger for Tablets and Cell Phones with Quick Charge 2.0 Technology, 6 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Works with any standard 12V DC vehicle power outlet
- LED indicates successful charging

Built-In USB Micro-B Cable with Quick Charge 2.0

- Quick Charge 2.0 Class A 5/9/12V technology
- Quick Charge 2.0 delivers up to 75% faster charging vs. conventional USB charging.
- Also charges non-QC devices at maximum power output of 5V 2.4A
- Coiled to take up less space than regular 6 ft. cable

Specifications

OVERVIEW	
UPC Code	037332196309
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Plug Type	Car Auxiliary Power Outlet
OUTPUT	
Overload Protection	Yes
CHARGING	
Charging Ports / Amps	(1) 2.4A; (1) 2A / 1.67A / 1.25A
Number of Charging Ports	1
Total Charging Amps	3.65A
Charging Method	USB
Total Charging Watts	27
Charging Ports Detail	USB-A: 5V/2.4A (12W)USB Micro-B: 5V/2A, 9V/1.67A, 12V/1.25A
Charging Port Type	USB A (FEMALE)
Charging Method Detail	Quick Charge 2.0
PHYSICAL	
Color	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	1.27 x 19.81 x 17.02
Shipping Dimensions (hwd / in.)	0.50 x 7.80 x 6.70
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	30% to 90% RH, Non-Condensing
CONNECTIONS	
Ports	1
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	MICRO-USB B (MALE)
FEATURES & SPECIFICATIONS	
Quick Charge Compliant	2.0
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, REACH, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U280-C02-S-M6](#)