

USB-C to VGA Adapter with USB-A Port and PD Charging, Black

MODEL NUMBER: **U444-06N-VUB-C**



USB-C to VGA mini dock adds VGA, USB-A and USB-C PD ports to your laptop, MacBook, Chromebook or other compatible device.

Features

USB 3.1 Type-C Mini Dock Connects to Your Device's USB-C or Thunderbolt 3 Port This USB 3.1 to VGA adapter helps you transmit video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a VGA-enabled television, monitor or projector. It's ideal for transmitting 1080p video to a large display, adding a thumb drive or other USB peripheral, and powering and charging a PD Charging-compliant mobile device—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting Video Signals With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 1080p Video to a VGA Display To send high-definition video to a VGA television, projector or monitor, connect the VGA port to the display using a VGA cable (sold separately). The VGA port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

Connects Keyboards, Thumb Drives and Other USB Peripherals The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer, and supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps. It is also backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host must support USB OTG (On-the-Go)

Charges the Connected Laptop, Smartphone or Other Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the USB-C mini dock is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W. This USB-C port is also capable of data transfer. **Note:** USB-C PD port does not support Quick Charge (QC).

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play Thunderbolt 3 and USB to VGA cord requires no software, drivers or external power. It's about the size of a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U444-06N-VUB-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Play 1080p video from your laptop or PC on a VGA display
- Give a video presentation at a meeting, training session, conference or trade show
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Edit large documents on two different monitors

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with VGA input (VGA port)

Package Includes

- U444-06N-VUB-C USB-C to VGA Adapter w/USB-A Hub and PD Charging - USB 3.1, Thunderbolt 3, 1080p, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332213242
Technology	USB 3.1 (Gen 1); USB; VGA/SVGA; PD Charging
Host Connector	USB C (MALE)
VIDEO	
Max Supported Video Resolution	VGA: 1920 X 1080 (1080P) @ 60HZ
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CHARGING	
Charging Ports / Amps	0.9A; 3A
Total Charging Watts	60
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Material of Construction	PVC, ABS
Shipping Dimensions (hwd / in.)	0.90 x 3.70 x 5.50
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.57 x 3.1 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	6.1 BTU/Hr
Power Consumption (Watts)	1.8
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB port, Up to 20V 3A (60W) Input (USB-C)
CONNECTIONS	
Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	USB 3.0 A (FEMALE)
Side B - Connector 3	USB Type-C (FEMALE)
Connector Plating	Nickel



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U444-06N-VUB-C](#)