

4-Port USB 3.0 SuperSpeed Hub for Data and USB Charging - USB-A, BC 1.2, 2.4A

MODEL NUMBER: U360-004-2F



Adds 4 new USB 3.0 ports to your computer, laptop, MacBook or Chromebook for connecting hard drives, smartphones and other USB devices.

Features

USB 3.0 Hub/Charger Adds up to 4 USB Devices to Your Computer, MacBook or Chromebook This four-port USB 3.0 hub connects directly to the USB-A port on your computer, laptop, MacBook, Ultrabook or Chromebook using the included cable. It allows you to use as many as four USB devices, such as flash drives, external hard drives, printers, barcode scanners and digital cameras, at the same time. Each USB port supports Battery Charging v1.2 (BC 1.2) standards for faster charging of mobile devices, including Apple and Android smartphones and tablets.

Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers The hub supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It is especially recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. The bus-powered hub distributes 900mA to its four ports. When using the included external power supply to draw additional power, the hub can provide up to 1.5A for fast charging of mobile devices. All four ports support BC 1.2 and 2.4A Quick Charge for Apple devices, up to a maximum of 3.5A total at any one time.

Plug-and-Play Hub Comes Ready to Connect Right Away The U360-004-2F works with all major operating systems and requires no software to download and install. It's backward compatible with previous USB versions, so you can also continue using older peripherals while getting maximum performance from current devices. Overcurrent and overvoltage safeguards protect your connected equipment against damage or data loss due to power surges.

Sleek and Slim Housing Designed for Everyday Workspace Use or Connecting on the Go The compact unit is designed for convenient positioning within your reach, making USB ports accessible while not taking up much workspace. It is also slim enough to pack in your pocket, purse or laptop bag for use in a hotel, conference room or airport as both a multiport hub and a USB charger.

Highlights

- Adds a printer, scanner, hard drive, webcam—up to 4 USB devices—to your computer
- Supports USB 3.0 SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- BC 1.2-compliant USB-A ports provide up to 3.5A total for charging mobile devices
- Compact hub fits easily in your purse, backpack or laptop bag for connecting on the go
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 4 USB devices to your PC, laptop, MacBook, Ultrabook or Chromebook's USB-A port
- Add easy-to-access USB ports to desktop computers that are in a cabinet, behind furniture or otherwise hard to reach
- Charge your smartphone or tablet
- Pack it in your laptop bag for quick connection of peripherals at a remote workspace or conference

System Requirements

- Compatible with all USB-enabled operating systems (USB 3.0 port needed to achieve USB 3.0 speeds)

Package Includes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- U360-004-2F 4-Port USB 3.0 SuperSpeed Hub
- USB-A to USB-B 3.0 cable, 4 ft.
- External power supply with 5 ft. cord (Input: 100–240V, 50/60 Hz, 0.6A; Output: 12V 2A)

Specifications

OVERVIEW	
UPC Code	037332217912
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A
Technology	USB; USB 3.0 (SuperSpeed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	Yes
Product Length (in.)	3.622
Product Length (cm.)	9.2
Product Length (ft.)	0.301
Product Length (m.)	0.092
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL
USB Power Delivery (PD) Charging Support	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports / Amps	(4) 1.5A
Charging Ports	(4) USB-A: 5V 1.5A (7.5W); 2.4A Quick Charge
Charging Ports Detail	All four ports up to a maximum of 3.5A total at any one time.
PHYSICAL	
Color	Black
Material of Construction	ABS, PBT
Unit Dimensions (hwd / in.)	.85 x 3.62 x 2.01
Unit Packaging Type	Box
Unit Weight (kg)	0.35
Unit Weight (lbs.)	0.7716
ENVIRONMENTAL	
Operating Temperature Range	41 to 104 °F (5 to 40 °C)
Storage Temperature Range	32 to 149 °F (0 to 65 °C)
Relative Humidity	20% to 80% RH, Non-Condensing
Power Provided to Connected Device(s)	0.9A (Bus-Powered), 1.5A (connected to external PSU)
CONNECTIONS	
Ports	4
Side A - Connector 1	USB B (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Connector Plating	Nickel



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH, FCC
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U360-004-2F](#)