

## 10-Port USB 3.0 SuperSpeed Hub with USB Charging

MODEL NUMBER: U360-010



Adds 10 new USB 3.0 ports to your computer, laptop, MacBook or Chromebook for connecting hard drives, smartphones and other USB devices.

### Features

**USB 3.0 Hub Adds up to 10 USB Devices to Your Computer, MacBook or Chromebook** This 10-port USB 3.0 hub connects directly to the USB-A port on your computer, laptop, MacBook, Ultrabook or Chromebook. It allows you to use as many as 10 USB devices, such as flash drives, external hard drives, printers, barcode scanners and digital cameras. Each USB port supports Battery Charging v1.2 (BC 1.2) standards for faster charging of mobile devices, such as Apple and Android smartphones and tablets.

**Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers** The hub supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It is especially recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. Each BC 1.2 port provides up to 1.5A for charging mobile devices. When the hub is connected to AC power, it can double as a USB charger providing up to 2.4A maximum power per port (total power available to all ports depends on the external power supply).

**Plug-and-Play Hub Comes Ready to Connect Right Away** The U360-010 works with all major operating systems and requires no software or drivers to download and install. The included external power supply comes with four international plug adapters that ensure you can use the hub almost anywhere. Plus, it's backward compatible with previous USB versions, so you can also continue using older peripherals while getting maximum performance from current devices. Overcurrent and overvoltage safeguards protect your connected equipment against damage or data loss due to power surges.

**Sleek and Slim Housing Designed for Everyday Workspace Use or Connecting on the Go** The compact unit is designed for convenient positioning within your reach, making USB ports accessible while not taking up much workspace. It is also slim enough to pack in your pocket, purse or laptop bag for use in a hotel, conference room or airport.

### Highlights

- Adds a printer, scanner, hard drive, webcam—up to 10 USB devices—to your computer
- Supports USB 3.0 SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- BC 1.2-compliant USB-A ports provide up to 5V 2.4A each for charging mobile devices
- Compact hub fits easily in your purse, backpack or laptop bag for connecting on the go
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect up to 10 USB devices to your PC, laptop, MacBook, Ultrabook or Chromebook's USB-A port
- Add easy-to-access USB ports to desktop computers that are in a cabinet, behind furniture or otherwise hard to reach
- Charge your smartphone or tablet
- Pack it in your laptop bag for quick connection of peripherals at a remote workspace or conference

### System Requirements

- Compatible with all USB-enabled operating systems (USB 3.0 port needed to achieve USB 3.0 speeds)

### Package Includes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- U360-010 10-Port USB 3.0 SuperSpeed Hub - USB Charging
- USB-A to USB-B 3.0 cable, 3 ft.
- External power supply (Input: 100–240V, 50/60 Hz, 0.8A; Output: 5V 4A)
- (4) International plug adapters (North America, U.K., Europe, Australia)

## Specifications

OVERVIEW	
UPC Code	037332221506
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A Max / Output: 5V, 4A
Over Current Protection	Y
Technology	USB; USB 2.0 (High Speed); USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(10) USB A (FEMALE)
Data Ports Details	(10) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
Bus Powered	No
Product Length (in.)	4.566
Product Length (cm.)	11.59



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Length (ft.)	0.38
Product Length (m.)	0.115
<b>POWER</b>	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
External Power Supply Output Specs (V / A)	5V / 4A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; GS; RoHS; TUV; UL; cUL
USB Power Delivery (PD) Charging Support	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>CHARGING</b>	
Charging Ports / Amps	2.4A
Charging Ports	USB-A: 5V 1.5A (7.5W); 2.4A Quick Charge
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS
Unit Dimensions (hwd / cm)	2.2 x 11.6 x 6.5
Unit Dimensions (hwd / in.)	0.87 x 4.6 x 2.6
Unit Packaging Type	Box
Unit Weight (kg)	0.37
Unit Weight (lbs.)	0.82
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	41 to 104 F (5 to 40 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	11.36 BTU/Hr
Power Consumption (Watts)	3.3



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Power Provided to Connected Device(s)	USB Only: 2.4A shared between all ports; Power Supply Only: 4.5A shared between all ports
<b>CONNECTIONS</b>	
Ports	10
Side A - Connector 1	USB 3.0 A (FEMALE)
Side B - Connector 1	(10) USB 3.0 A (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 1.1 (up to 12 Mbps); USB 2.0 (up to 480 Mbps); USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U360-010](#)