

3-Port USB-C Hub - 3x USB-A, GbE, 60W PD Charging, Black

MODEL NUMBER: **U460-003-3AGB-C**



USB 3.1 hub adds USB-A, Gigabit Ethernet and USB-C charging ports to your laptop, MacBook or other compatible device.

Features

USB-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port This USB 3.1 hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for connecting to a wired Gigabit Ethernet network, adding a thumb drive and other USB peripherals, and powering and charging a PD Charging-compliant mobile device—all at the same time.

Accesses a Wired Gigabit Ethernet Network The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Connects Up to 3 USB-A Peripherals Three USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and the dedicated fast-charging port provides up to 5V 1.5A (7.5W) for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host must support USB OTG (On-the-Go).

Charges a Connected Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the USB-C network adapter is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W. **Note:** USB-C PD port does not support Quick Charge (QC).

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB 3.1 hub requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go. Plug it into your laptop for instant network connection.

Highlights

- Connects you to a wired Ethernet network when Wi-Fi is slow or unavailable
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Accepts up to 3 USB peripherals, turning your laptop into a mini workstation
- USB-A fast-charging port provides up to 5V 1.5A (7.5W) of power
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks

Applications

- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your notebook or download data from the Ethernet at true 10/100/1000 Mbps Ethernet speeds
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Package Includes

- U460-003-3AGB-C 3-Port USB-C Hub, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332209184
Product Type	Hub
Technology	Cat5/5e; Cat6; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB; PD Charging
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Power Delivery (PD) Charging Support	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), Orange (Activity)
CHARGING	
Charging Ports / Amps	(2) 0.9A; (1) 1.5A; (1) 3A
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W)
Total Charging Watts	60
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.50
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.65 x 3.8 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	8.5 BTU/Hr
Power Consumption (Watts)	2.5
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5A) Output USB port
COMMUNICATIONS	
Network Speed	Gigabit Ethernet (10/100/1000)
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U460-003-3AGB-C](#)