

Molded Parts

Specification Control Drawing

Part Number : 202F2XX-X-02
Description : Boot, Straight, With Lip

NOTES

1. All dimensions are in $\frac{\text{inches}}{\text{[millimeters]}}$
2. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. "S" & "T" dimensions apply to a minimum of 240° of the circumference.




TABLE OF DIMENSIONS											
PART NUMBER	H		J		P	R	JO	HW	JW	S	T
	Min	Max	Min	Max	±10%	±10%	±10%	+0.06/-0.03	±0.03	+0.06/-0.03	±0.03
	a	b	a	b	b	b	b	b	b	b	b
202F211-X-02	$\frac{.94}{[23,9]}$	$\frac{.39}{[9,9]}$	$\frac{.68}{[17,3]}$	$\frac{.26}{[6,6]}$	$\frac{3.00}{[76,2]}$	$\frac{.46}{[11,7]}$	$\frac{2.23}{[56,6]}$	$\frac{.06}{[1,5]}$	$\frac{.06}{[1,5]}$	$\frac{.06}{[1,5]}$	$\frac{.05}{[1,3]}$
202F232-X-02	$\frac{1.22}{[31,0]}$	$\frac{.73}{[18,5]}$	$\frac{.96}{[24,4]}$	$\frac{.35}{[8,9]}$	$\frac{1.50}{[38,1]}$	$\frac{.48}{[12,2]}$	$\frac{.50}{[12,7]}$	$\frac{.07}{[1,8]}$	$\frac{.06}{[1,5]}$	$\frac{.07}{[1,8]}$	$\frac{.05}{[1,3]}$
202F253-X-02	$\frac{1.53}{[38,9]}$	$\frac{1.11}{[9,9]}$	$\frac{1.24}{[31,5]}$	$\frac{.43}{[10,9]}$	$\frac{4.50}{[114,3]}$	$\frac{.55}{[14,0]}$	$\frac{3.10}{[78,7]}$	$\frac{.07}{[1,8]}$	$\frac{.06}{[1,5]}$	$\frac{.07}{[1,8]}$	$\frac{.07}{[1,8]}$

If this document is printed it becomes uncontrolled. Check for the latest revision

Molded Parts

Specification Control Drawing

Part Number : 202F2XX-X-02
Description : Boot, Straight, With Lip

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-51	Flexible EPB	RT-1321	/164	S-1124	Adhesive
-770	NBCCS	RT-770 TYPE II	N.A.		

ORDERING INFORMATION

202F2XX

-51

-02

/164

-0

Base part number

Material dash number
(See Compatability Chart)

Modification number

Adhesive slash number
(If necessary, see Compatability Chart)

Color Designator

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION



TYCO ELECTRONICS
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : E
Date : 11/15/06

MP060146

Part Number : 202F2XX-X-02
Description : Boot, Straight, With Lip

If this document is printed it becomes uncontrolled. Check for the latest revision

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202F211-50-22-0](#) [202F211-51/164-0-CS8112](#) [202F211-51-02-0-CS5422](#) [202F211510CS5326](#)