


# Molded Parts Specification Control Drawing

Part Number : 202G2XX  
Description : Boot, Straight, With Lip

## NOTES

- All dimensions are in  $\frac{\text{inches}}{[\text{millimeters}]}$
  - Dimensions appearing in table are as follows:
    - As Supplied
    - After Unrestricted Recovery
  - Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- ⚠ On part 202G211, wall thickness will not be measured in transition area.



PART NUMBER	H		J		P	R	S	T	JO	HW	JW
	Min a	Max b	Min a	Max b							
202G211	.94 [23,9]	.39 [9,9]	.94 [23,9]	.29 [7,4]	4.17 [105,9]	.46 [11,7]	.04 [1,0]	.05 [1,3]	3.40 [86,4]	.04 [1,0]	.03 [0,7]
202G221	1.07 [27,2]	.52 [13,2]	1.07 [27,2]	.33 [8,4]	4.77 [121,2]	.48 [12,2]	.04 [1,0]	.05 [1,3]	3.44 [87,4]	.04 [1,0]	.03 [0,7]
202G232	1.22 [31,0]	.73 [18,5]	1.22 [31,0]	.37 [9,4]	5.46 [138,7]	.48 [12,2]	.04 [1,0]	.05 [1,3]	4.11 [104,4]	.04 [1,0]	.03 [0,7]
202G242	1.25 [31,7]	.87 [22,1]	1.25 [31,7]	.42 [10,7]	6.28 [159,5]	.48 [12,2]	.04 [1,0]	.06 [1,5]	4.90 [124,5]	.04 [1,0]	.03 [0,7]
202G253	1.53 [38,9]	1.11 [28,2]	1.53 [38,9]	.47 [11,9]	7.00 [177,8]	.42 [10,6]	.05 [1,3]	.07 [1,8]	5.65 [143,5]	.05 [1,3]	.04 [1,0]

**tyco** Raychem  
**Electronics**

TYCO ELECTRONICS  
300 CONSTITUTION DRIVE  
MENLO PARK, CALIFORNIA 94025


Revision : H  
Date : 2/17/05

Part Number : 202G2XX  
Description : Boot, Straight, With Lip

# Molded Parts Specification Control Drawing

Part Number : 202G2XX  
Description : Boot, Straight, With Lip

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-55	Fluoropolymer	RT-1330	N/A		
-780	NBCCS	RT-780 TYPE II	N/A		
-790	NBCCS	RT-790 TYPE II	N/A		



THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

**tyco** Raychem  
**Electronics**

TYCO ELECTRONICS  
300 CONSTITUTION DRIVE  
MENLO PARK, CALIFORNIA 94025

Revision : H  
Date : 2/17/05

Part Number : 202G2XX  
Description : Boot, Straight, With Lip

If this document is printed it becomes uncontrolled.  
Check for the latest revision.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202G242-55-0](#) [202G253-55-0](#)