





- ① HOUSING: LCP, UL94V0, COLOR: BLACK.  
CONTACT: PHOSPHOR BRONZE.
- ② FINISH: 1.27 $\mu$ m GOLD IN CONTACT AREA 1.27 $\mu$ m  
MIN. TIN-LEAD ON PCB TAIL OVER 3.81 $\mu$ m MIN.  
NICKEL OVER ALL.
- ③ FINISH: 1.27 $\mu$ m GOLD IN CONTACT AREA 1.27 $\mu$ m  
MIN. TIN ON PCB TAIL OVER 3.81 $\mu$ m MIN.  
NICKEL OVER ALL.
- ④ PLATE THROUGH HOLE PER TE SPEC. 114-13056  
FIGURE 4.
- ⑤ ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA  
REQUIRED IF CONNECTOR-SIDE EXTRACTION  
TOOL IS TO BE USED.
6. POSITIONS A9, A11, A13, B9, B11, B13, C10, C12,  
D10, D12, E9, E11, E13, F9, F11, F13, G10, G12,  
H10 & H12 ARE NOT LOADED.



|                                                                                       |           |
|---------------------------------------------------------------------------------------|-----------|
|  | 2292402-2 |
|  | 2292402-1 |
| PLATING                                                                               | PART NO   |

|                                                                                                            |  |                                                                                                                    |  |                                                                                                             |  |
|------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                     |  | DWN C. C. THOMAS 5-6-15<br>CHK CHS 5-6-15<br>APP'D D. HOANG 5-6-15                                                 |  |  TE Connectivity       |  |
| DIMENSIONS:<br>mm<br> |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±0.5<br>2 PLC ±0.13<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±0° |  | NAME<br>CONNECTOR ASSEMBLY, BACKPLANE<br>VERTICAL RECEPTACLE, CENTER,<br>20.3mm, MultiGig RT 2, SELECT LOAD |  |
| MATERIAL<br>          |  | FINISH<br>                    |  | PRODUCT SPEC<br>108-2072<br>APPLICATION SPEC<br>114-13056<br>WEIGHT -<br>CUSTOMER DRAWING                   |  |
|                                                                                                            |  |                                                                                                                    |  | SIZE CASE CODE DRAWING NO<br>A100779C=2292402<br>RESTRICTED TO -<br>SCALE 8:1 SHEET 1 OF 1 REV              |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2292402-2](#)