


LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECO-13-000800	16JAN12	KH	PO



SPECIFICATIONS:

MATERIAL: PHENOLIC , COLOR: BLACK.
SHAFT HOLE INSERT: COPPER ALLOY.
SET SCREW: #6-32 UNC-2A
PKES60B, PKES70B, PKES90B, AND PKES120B
ONE SET SCREW ONLY.
PKES140B AND PKES150B, TWO SET SCREWS ONLY.



NOTES:

- INTERPRET DRAWING PER ASME Y14.5M-1994.
- DECORATIVE SPUN ALUMINUM INLAY.
- PLASTIC OVERLAY MUST BE PRESENT ON TOP SURFACE.
- PACKAGING: FOR P/N PKES140B-1/4 & PKES120B-1/4, A CARDBOARD SHEET SHALL BE INSERTED BETWEEN THE OUTER SLEEVE & KNOB TRAY SO AS TO PREVENT THE KNOBS FROM FALLING OUT OF THEIR RESPECTIVE POCKETS.
- VOID CORING FROM BOTTOM SIDE OF KNOB OPTIONAL.
- DIMENSIONS DO NOT APPLY IN MOLD GATE AREA.

P/N	MODEL	SHAFT HOLE Ø	TOLERANCES UNLESS OTHERWISE SPECIFIED:							
			"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"
5-1437624-1	PKES60B1/8	.126	.748	.618	.400	.460	.090	.220	.370	.470
5-1437624-0	PKES60B1/4	.251	.748	.618	.400	.460	.090	.220	.370	.470
5-1437624-2	PKES70B1/4		.855	.744	.508	.705	.080	.275	.421	.526
5-1437624-3	PKES90B1/4		1.012	.889	.623	.846	.079	.256	.500	.570
4-1437624-6	PKES120B1/4		1.296	1.160	.858	1.018	.118	.320	.500	.628
4-1437624-7	PKES140B1/4		1.500	1.374	1.094	1.217	.118	.280	.540	.693
4-1437624-8	PKES150B1/4		1.768	1.551	1.217	1.413	.118	.300	.733	.831

TOLERANCE CHART		
SHAFT HOLE	DIMENSION	TOLERANCE
	.126 DIA.	+.003 -.000
	.251 DIA.	+.003 -.000

WAS DWG 80444

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV		14JUL04				TE Connectivity					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK —		NAME							
		APVD M ZITTO		—		KNOB, FLUTED WITH SKIRT (PKES60, PKES70, PKES90, PKES120, PKES140 & PKES150)							
		PRODUCT SPEC		—									
		APPLICATION SPEC		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		MATERIAL SEE SPECIFICATIONS		FINISH —		WEIGHT —		A2		00779		C=4-1437624-6	
CUSTOMER DRAWING						SCALE 1:1		SHEET 1 of 1		REV A2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PKES60B1/8](#)