


PROPERTY OF DEUTSCH E.C.D


THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT SHALL NOT BE DISCLOSED, DUPLICATED, NOR USED IN WHOLE OR IN PART FOR ANY PURPOSE OTHER THAN TO EVALUATE THIS DRAWING.



- DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
 - INSERT ARRANGEMENT PER MIL-STD-1554.
 - LEAK RATE: < 1E-8 cc/sec He @ 1 atm.
 - INSULATION RESISTANCE: >5000 MEGOHM @ 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: NO BREAKDOWN @ 1500 VAC
 - MATERIAL:
SHELL - C1215 STEEL
INSULATOR - COMPRESSION GLASS INSERT
CONTACT - 52 HIGH NICKEL-IRON ALLOY
INTERFACIAL SEAL - SILICONE ELASTOMER
O-RING - ETHYLENE PROPYLENE
 - FINISH:
SHELL & CONTACTS - ELECTRODEPOSITED TIN OVER NICKEL PLATE
 - CONFORMS TO MIL-C-26500 & MS24264H EXCEPT AS NOTED.
- NOTE(S):

C 43082-10B20PN

REVISIONS			
REV	DESCRIPTIONS	DATE	APPROVED
A	REVISED PER E.O. H2719	5/26/99	L. STOLLE
B	REVISED PER E.O. H2797	7-30-99	L. STOLLE
C	REVISED PER E.O. H2904	12-13-99	L. Stolle



CUSTOMER P/N	DEUTSCH P/N
37-01714	43082-10B20PN

FILE: 43082-10B20PN-ENV

SIGNATURE & DATE		RECEPTACLE, CONNECTOR		CP	MATL CODE 74
DR	P. COVARRUBIAS 2-22-99	HERMETIC BAYONET COUPLING SQUARE FLANGE MOUNT 10-20 ARRANGEMENT 2 SIZE 16 EYELET PINS		DEUTSCH HERMETIC PRODUCTS OPERATION 250 Eddie Jones Way Oceanside, CA 92054	
CHK	L. STOLLE 3-9-99				
PE	J. AGUILERA 3-9-99			B 43082-10B20PN CAGE CODE 11139	
APPD	J. AGUILERA 3-9-99				
SCALE:		ENVELOPE		DWG SIZE	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[43082-10B20PN](#)