





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			NC	NEW RELEASE PER E.O. P15607	15MAY1998	JW	RDR
			A	REVISED PER E.O. P15939	06APR1999	RO	RDR
			B	REVISED PER E.O. P20700	09NOV2010	IG	RDR
			C	REVISED PER ECO-14-019072	23FEB2015	JA	DM



SCALE 1:1

- 6 PART MODIFICATION: BACKSHELL ADAPTER ACCEPTS BACKSHELLS:
2428-004-2405, 2428-008-2405
2428-010-2405, 2428-011-2405
- 5 NOTED DIMENSION DOES NOT INCLUDE GROMMET PROTRUSION.
- 4 MATERIAL: PLUG HOUSING/COUPLING RING: PA66 GF10 (BLACK)
BACKSHELL ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)

- 3 SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS

2. THIS PLUG MATES WITH HDP24-24XXP/SX-XXXX RECEPTACLE
X = SEAL TYPE (N,T,E)
XX = INSERT ARRANGEMENT
XXXX = MODIFICATION

- 1 SEE CUSTOMER DRAWING 0425-014-2400 FOR AVAILABLE INSERT ARRANGEMENTS AND PART NUMBERS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. OCHOA 24MAR1999		TE TE Connectivity	
DIMENSIONS: INCHES[mm]		CHK BRICE BYFORD 09NOV2010			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STEVE BEARD 08NOV2010		NAME	
0 PLC ±		PRODUCT SPEC 0425-021-0000		PLUG, COUPLING RING	
1 PLC ±		APPLICATION SPEC 3		SIZE 24, -L017 MOD	
2 PLC ±				HDP SERIES	
3 PLC ±				SIZE CAGE CODE DRAWING NO RESTRICTED TO	
4 PLC ±				A3 4AFU8 C-HDP26-24-XXP/SX-L017 -	
ANGLES ±				SCALE 2:1 SHEET 1 OF 1 REV C	
FINISH N/A		WEIGHT			
MATERIAL 4		Customer Drawing			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HDP26-24-33PN-L017](#)