

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-		Released per ECO-17-012177	08/17/17	J.B TL

SCT
Splice Cover (Dual Wall)
Heat-Shrinkable Tubing




Table 1: Dimensions mm(inches)

Size	As Supplied	As Recovered		
	Minimum Expanded I.D. (D)	Maximum Recovered I.D. (d)	Recovered Total Wall (W)	Minimum Recovered Adhesive Wall (W1)
No. 0	5.10 (0.200)	1.30 (0.050)	1.40 (0.055) ± 0.30 (0.012)	0.76 (0.030)
No. 1	7.62 (0.300)	1.65 (0.065)	1.52 (0.060) ± 0.30 (0.012)	0.76 (0.030)
No. 2	9.02 (0.355)	2.29 (0.090)	1.52 (0.060) ± 0.30 (0.012)	0.76 (0.030)
No. 3	11.56 (0.455)	2.54 (0.100)	2.29 (0.090) ± 0.30 (0.012)	1.40 (0.055)
No. 3A	14.10 (0.555)	3.00 (0.118)	2.24 (0.088) ± 0.30 (0.012)	1.40 (0.055)
No. 4	17.78 (0.700)	4.45 (0.175)	2.54 (0.100) ± 0.30 (0.012)	1.52 (0.060)
No. 5	27.94 (1.100)	8.38 (0.330)	2.54 (0.100) ± 0.30 (0.012)	1.52 (0.060)
No. 7	33.02 (1.300)	12.70 (0.500)	1.91 (0.075) ± 0.20 (0.008)	0.92 (0.036)

Color: Jacket shall be black; adhesive liner shall be amber. Marking is SCT-0, SCT-1, SCT-2, SCT-3, SCT-4, SCT-5 and SCT-7. Size SCT-3A is not printed.


Reference Specification TEC-108-120012

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 2017 TE Connectivity

DIMENSIONS: mm	DWN J. Bitter	01-JUN-17	 TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA			
	CHK T. Licko	27-JUN-17				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. Licko	27-JUN-17	NAME SCT Splice Cover Dual Wall Heat-Shrinkable Tubing			
	PRODUCT SPEC	-				
0 PLC ± -	APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1 PLC ± -	WEIGHT	0	A4	06090	SCT	
2 PLC ± -	CUSTOMER DRAWING		SCALE	None	SHEET	1 of 1
3 PLC ± -					REV	L
4 PLC ± -						
ANGLES ± -						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SCT-NO.1-E6-0-27MM](#)