








RJ45, CAT6a FEEDTHROUGH CONNECTOR GROUNDED TO OUTER SHELL DATA TRANSFER RATE TESTED TO 10 GIGABIT CONTACT SALES OFFICE FOR TEST RESULTS




OPTION W




OPTION Y



OPTION Z



005 - CABLE SEALING OPTION



BT - BOOT OPTION

PC4B0034(S)-19NX-1-C(-BT)

NOTES
MIL-DTL-38999 STYLE
MATES WITH AMPHENOL RJFTV

FINISH
SEE TABLE
MATERIALS
RJ45
CONTACTS COPPER WITH SELECTIVE GOLD PLATE
SHIELDING - NICKEL PLATED BRASS
BODY - PA, UL94V-0
PCB - FR4, UL94V-0

SEAL - SILICONE ELASTOMER
INSULATOR - PPS GL40 UL94, COLOUR BLACK
POTTING - QSIL 550 UL94V-0

PERFORMANCE
VOLTAGE RATING 50V DC / 35V AC
TEMPERATURE -40°C TO +120°C

SEALING (UNMATED)
S = PRESSURE TESTED TO 1 BAR

SERIES
SEALING OPTION (SEE NOTES)
(OMIT FOR STANDARD IP68 SEALED WHEN MATED)
SHELL SIZE
KEY ARRANGEMENT (N, A, B, C, D, E)
INSERT ROTATION (W, X, Y, Z)
MATERIAL/PLATING (SEE TABLE)
BACKSHELL OPTION (005 = CABLE SEAL, BT = BOOT)
PART NUMBER FOR UNGROUNDED VERSION: PC4B0034-19NX-1-C-U

CODE	MATERIAL / FINISH
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZK	ALUMINIUM / ZINC COBALT BLACK OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST

LIST NOT EXHAUSTIVE, FOR COMPREHENSIVE LIST AND SPECS, SEE WEBSITE

DRAWN	M.PAUL	DATE	13/04/2017	 3RD ANGLE PROJECTION NOT TO SCALE UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1° MATERIAL SEE PART NUMBER BREAKDOWN FINISH SEE PART NUMBER BREAKDOWN
SALES APPR	ADP	DATE	13/04/2017	
DESIGN APPR				
PROD APPR				
QUAL APPR				
ISSUE	REV.	DCR	6453	
2				
NCAGE CODE U5792		WEIGHT		

PART NUMBER:	PC4B0034-19xx-x-x
TITLE:	CAT6A RJ45 SOLDER RECEPTACLE ASSEMBLY
ASSY USED ON:	CAT6A D38999/20
THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	

POLAMCO LTD, WESTON LOCK,
LOWER BRISTOL ROAD
BATH BA2 1EP

SHT
1

DRAWING NO:
C3176



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PC4B0034-19NX-1-C](#) [PC4B0034-19NX-4-J](#)