

TE P/N	TE CD	Nanonics P/N	Part Description
1589060-1	1589060	QCM007SC2DC003P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 3 inches, panel mount.
1589060-2	1589060	QCM007SC2DC004P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 4 inches, panel mount.
1589060-3	1589060	QCM007SC2DC006P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, panel mount.
1589060-4	1589060	QCM007SC2DC012P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, panel mount.
1589060-7	1589060	QCM007SC2DC036P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 36 inches, panel mount.
1589060-9	1589060	QCM007SC2DCC30P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 30 centimeters, panel mount.
1-1589060-0	1589060	QCM007SC2DM003P	Quick disconnect, circular, metal, 7 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 3 inches, panel mount.
1-1589060-1	1589060	QCM007SC2DC020P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 20 inches, panel mount.
1-1589060-2	1589060	QCM007SC2DYC15P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, white PTFE M16878/6 wire, 15 centimeters, panel mount.
1-1589060-3	1589060	QCM007SC2DYM1.5P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, white PTFE M16878/6 wire, 1.5 meters, panel mount.
1-1589060-4	1589060	QCM007SC2DCC15P	Quick disconnect, circular, metal, 7 position, receptacle, 30awg 7 strand, color coded PTFE wire, 15 centimeters, panel mount.
1-1589060-5	1589060	QCM007SC2DYM02P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, white PTFE M16878/6 wire, 2 meters, panel mount.
1-1589060-6	1589060	QCM007SC2DY012P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, white PTFE M16878/6 wire, 12 inches, panel mount.
1-1589060-7	1589060	QCM007SC2DC024P	Quick disconnect, circular, metal, 7 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches, panel mount.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM007SC2DYC15P](#)