

TE P/N	TE CD	Nanonics P/N	Part Description
1589062-1	1589062	QCM044SC2DC003P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 3 inches, panel mount.
1589062-2	1589062	QCM044SC2DC006P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, panel mount.
1589062-3	1589062	QCM044SC2DC012P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, panel mount.
1589062-5	1589062	QCM044SC2DC036P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 36 inches, panel mount.
1589062-6	1589062	QCM044SC2DMC16P	Quick disconnect, circular, metal, 44 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 16 centimeters, panel mount.
1589062-7	1589062	QCM044SC2DMC46P	Quick disconnect, circular, metal, 44 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 46 centimeters, panel mount.
1589062-8	1589062	QCM044SC2DC018P	Quick disconnect, circular, metal, 44 position, receptacle, 30AWG 7 strand, color coded PTFE wire, 18 inches, panel mount.
1589062-9	1589062	QCM044SC2DM036P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches, panel mount.
1-1589062-0	1589062	QCM044SC2DM120P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 120 inches, panel mount.
1-1589062-1	1589062	QCM044SC2DC080P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 80 inches, panel mount.
1-1589062-2	1589062	QCM044SC2DC020P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 20 inches, panel mount.
1-1589062-3	1589062	QCM044SC0DM036P	Quick disconnect, circular, metal, 44 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches, panel mount.
1-1589062-4	1589062	QCM044SC0DM048P	Quick disconnect, circular, metal, 44 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 48 inches, panel mount.
1-1589062-5	1589062	QCM044SC0DM060P	Quick disconnect, circular, metal, 44 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 60 inches, panel mount.
1-1589062-6	1589062	QCM044SC2DC024P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches, panel mount.
1-1589062-7	1589062	QCM044SC2DMC50P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 50 centimeters, panel mount.
1-1589062-8	1589062	QCM044SC2DMM01P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 1 meter, panel mount.
1-1589062-9	1589062	QCM044SC2DM012P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, panel mount.
2-1589062-0	1589062	QCM044SC2DMC20P	Quick disconnect, circular, metal, 44 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 20 centimeters, panel mount.
2-1589062-1	1589062	QCM044SC2DM006P	Quick disconnect, circular, metal, 44 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 6 inches, panel mount.
2-1589062-2	1589062	QCM044SC0DX012P	Quick disconnect, circular, metal, 44 position, receptacle, 28 AWG solid, white PTFE wire, 12 inches, panel mount.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM044SC2DM120P](#)