

TE P/N	TE CD	Nanonics P/N	Part Description
1589071-1	1589071	303-0047-18	OBsolete
1589071-2	1589071	303-0047-20	OBsolete
1589071-3	1589071	CX030SC2RG006N	Coax, 50 ohm, 3 position, receptacle, 30 AWG RG-178 coaxial cable, 6 inches, thread for 1.0 jackscrews.
1589071-4	1589071	CX030SC2RG012	Coax, 50 ohm, 3 position, receptacle, 30 AWG RG-178 coaxial cable, 12 inches.
1589071-5	1589071	CX040SC2RG012	Coax, 50 ohm, 4 position, receptacle, 30 AWG RG-178 coaxial cable, 12 inches.
1589071-6	1589071	CX090SC2RG036N	Coax, 50 ohm, 9 position, receptacle, 30AWG RG-178 coaxial cable, 36 inches, thread for 1.0 jackscrews.
1589071-7	1589071	CX040SC2RG024N	Coax, 50 ohm, 4 position, receptacle, 30AWG RG-178 coaxial cable, 24 inches, thread for 1.0 jackscrews..
1589071-8	1589071	CX020SC2RG024N	Coax, 50 ohm, 2 position, receptacle, 30 AWG RG-178 coaxial cable, 24 inches, thread for 1.0 jackscrews.
1589071-9	1589071	CX080SC2RG024N	Coax, 50 ohm, 8 position, receptacle, 30AWG RG-178 coaxial cable, 24 inches, thread for 1.0 jackscrews.
1-1589071-7	1589071	CX080SC2RG015N	Coax, 50 ohm, 8 position, receptacle, 30 AWG RG-178 coaxial cable, 15 inches, thread for 1.0 jackscrews.
1-1589071-8	1589071	CX030SC2RG012N	Coax, 50 ohm, 3 position, receptacle, 30AWG RG-178 coaxial cable, 12 inches, thread for 1.0 jackscrews.
1-1589071-9	1589071	CX050SC2RG006N	Coax, 50 ohm, 5 position, receptacle, 30AWG RG-178 coaxial cable, 6 inches, thread for 1.0 jackscrews.
2-1589071-0	1589071	CX020SC2RG012N	Coax, 50 ohm, 2 position, receptacle, 30 AWG RG-178 coaxial cable, 12 inches, thread for 1.0 jackscrews.
2-1589071-1	1589071	CX030SC2RG060N	Coax, 50 ohm, 3 position, receptacle, 30 AWG RG-178 coaxial cable, 60 inches, thread for 1.0 jackscrews.
2-1589071-2	1589071	CX020SC2RG060N	Coax, 50 ohm, 2 position, receptacle, 30 AWG RG-178 coaxial cable, 60 inches, thread for 1.0 jackscrews.
2-1589071-3	1589071	CX010SC2RG048Q	Coax, 50 ohm, 1 position, receptacle, 30AWG RG-178 coaxial cable, 48 inches, thread for 1.2 jackscrews.
2-1589071-4	1589071	CX080SC2RG012N	Coax, 50 ohm, 8 position, receptacle, 30 AWG RG-178 coaxial cable, 12 inches, thread for 1.0 jackscrews.
2-1589071-5	1589071	CX020SC2RG018N	Coax, 50 ohm, 2 position, receptacle, 30 AWG RG-178 coaxial cable, 18 inches, thread for 1.0 jackscrews.
2-1589071-6	1589071	CX060SC2RG012Q	Coax, 50 ohm, 6 position, receptacle, 30AWG RG-178 coaxial cable, 12 inches, thread for 1.2 jackscrews.
2-1589071-7	1589071	CX080SC2RG012Q	Coax, 50 ohm, 8 position, receptacle, 30 AWG RG-178 coaxial cable, 12 inches, thread for 1.2 jackscrews.
2-1589071-8	1589071	CX020SC2RG024Q	Coax, 50 ohm, 2 position, receptacle, 30 AWG RG-178 coaxial cable, 24 inches, thread for 1.2 jackscrews.
2-1589071-9	1589071	CX040SC2RG012N	Coax, 50 ohm, 4 position, receptacle, 30 AWG RG-178 coaxial cable, 12 inches, thread for 1.0 jackscrews.
3-1589071-0	1589071	CX040SC2RG020N	Coax, 50 ohm, 4 position, receptacle, 30 AWG RG-178 coaxial cable, 20 inches, thread for 1.0 jackscrews.
3-1589071-1	1589071	CX050SC2RG01Q	Coax, 50 ohm, 5 position, receptacle, 30 AWG RG-178 coaxial cable, 1 meter, thread for 1.2 jackscrews.
3-1589071-2	1589071	CX090SC2RG030Q	Coax, 50 ohm, 9 position, receptacle, 30 AWG RG-178 coaxial cable, 30 inches, thread for 1.2 jackscrews.
3-1589071-3	1589071	CX030SC2RG020Q	Coax, 50 ohm, 3 position, receptacle, 30 AWG RG-178 coaxial cable, 20 inches, thread for 1.2 jackscrews.
3-1589071-4	1589071	CX030SC3CW018N	Coax, 50 ohm, 3 position, receptacle, 32 AWG FEP insulated coaxial cable, 18 inches, thread for 1.0 jackscrews.
3-1589071-5	1589071	CX060SC2RG012N	Coax, 50 ohm, 6 position, receptacle, 30AWG RG-178 coaxial cable, 12 inches, thread for 1.0 jackscrews.
3-1589071-6	1589071	CX030SC2RGM03N	Coax, 50 ohm, 3 position, receptacle, 30 AWG RG-178 coaxial cable, 3 meters, thread for 1.0 jackscrews

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CX080SC2RG012Q](#)