



1. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
 2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
 3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".
1. 材料: ガラス入り熱可塑性ポリエステル樹脂(94V-0), 色: 黒
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
3. Y KEY形状は、X KEY形状と左右対称

AS SHOWN 20POS(X-KEY) : 1-1903130-0

20	Y	9	22.5	26.0	27.6	26.2	2-1903130-0
20	X	9	22.5	26.0	27.6	26.2	1-1903130-0
12	Y	5	12.5	16.0	17.6	16.2	2-1903130-6
12	X	5	12.5	16.0	17.6	16.2	1-1903130-6
8	Y	3	7.5	11.0	12.6	11.2	2-1903130-4
8	X	3	7.5	11.0	12.6	11.2	1-1903130-4
6	Y	2	5.0	8.5	10.1	8.7	2-1903130-3
6	X	2	5.0	8.5	10.1	8.7	1-1903130-3
4	X	1	2.5	6.0	7.6	6.2	1-1903130-2
POS	KEY	n	A	B	C	D	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 純
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差 ±0.3, ±3°
0-PLC ±
1-PLC ±
2-PLC ±
3-PLC ±
4-PLC ±
ANGLES ±
FINISH 仕上

DWN
M. MAEBASHI 11APR2006

CHK
T. KUDO 11APR2006

APVD
D. MITSUGI 11APR2006

PRODUCT SPEC
108-78268, 78298

APPLICATION SPEC
取付適用規格
114-5377

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称

DYNAMIC D1200D 2.5mm PITCH
TAB HSG, FREE HANGING TYPE
4-20 POS

SIZE
寸法

CAGE CODE
番号

DRAWING NO
番付

RESTRICTED TO

SCALE
尺度

5:1

SHEET
張

1

OF
2

REV
C

1471-9 (2/09)
Pro/ENGINEER DRAWING

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS
表紙

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 2

C

B

2.5Xn=A

12POS(X-KEY): I-1903130-6

C

B

2.5Xn=A

8POS(X-KEY): I-1903130-4

C

B

2.5Xn=A

6POS(X-KEY): I-1903130-3

C

B

2.5Xn=A

4POS(X-KEY): I-1903130-2

9

X

↓

D1200

6

5

4

3

2

1

D

4

X

↓

D1200

4

3

2

1

D

3

X

↓

D1200

3

2

1

D

2

X

↓

D1200

2

1

D

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 純

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH 仕上

MATERIAL
材料

DWN
M. MAEBASHI 11APR2006

CHK
T. KUDO 11APR2006

APVD
D. MITSUGI 11APR2006

PRODUCT SPEC
製品規格 108-78268, 78298

APPLICATION SPEC
取付適用規格 114-5377

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称

DYNAMIC D1200D 2.5mm PITCH
TAB HSG, FREE HANGING TYPE
4-20 POS

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

SCALE
尺度 5:1

SHEET 2 OF 2

REV C

1471-9 (2/09)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1903130-4](#)