

© 2020

TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	5	INITIAL CUSTOMER DRAWING	01MAY2020	AFK	LS

VIEW A:
LAYING DIAGRAM

MATERIAL LIST
1. PAPER CARRIER - WHITE
2. CABLE LABEL

PRODUCT CODE	PRODUCT PITCH	No. HOLES	LABEL LENGTH	PRINTABLE LENGTH	LABEL HEIGHT
HLX104**TS025	12.7 (1/2")	4	45	25	10.4
HLX104**TS033	12.7 (1/2")	4	53	33	10.4
HLX104**TS038	12.7 (1/2")	4	58	38	10.4
HLX104**TS050	12.7 (1/2")	4	70	50	10.4
HLX104**TS070	12.7 (1/2")	4	90	70	10.4
HLX150**TS025	25.4 (1")	4	45	25	15.0
HLX150**TS033	25.4 (1")	4	53	33	15.0
HLX150**TS038	25.4 (1")	4	58	38	15.0
HLX150**TS050	25.4 (1")	4	70	50	15.0
HLX150**TS070	25.4 (1")	4	90	70	15.0
HLX203**TS025	25.4 (1")	4	45	25	20.3
HLX203**TS033	25.4 (1")	4	53	33	20.3
HLX203**TS038	25.4 (1")	4	58	38	20.3
HLX203**TS050	25.4 (1")	4	70	50	20.3
HLX203**TS070	25.4 (1")	4	90	70	20.3
HLX253**TS025	50.8 (2")	4	45	25	25.3
HLX253**TS033	50.8 (2")	4	53	33	25.3
HLX253**TS038	50.8 (2")	4	58	38	25.3
HLX253**TS050	50.8 (2")	4	70	50	25.3
HLX253**TS070	50.8 (2")	4	90	70	25.3

NOTES:-
1. NO ACCUMULATIVE ERROR THROUGH PACK IS ACCEPTABLE
2. PACKAGING AS REQUIRED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
AFK
CHK
L.SMITH
APVD
L.SMITH
PRODUCT SPEC
RW-2529
APPLICATION SPEC
411-121000
WEIGHT
VARIOUS

30APR2020
01MAY2020
01MAY2020

CUSTOMER DRAWING

TE Connectivity

PRE TAPED LFH THERMAL TRANSFER
CABLE LABEL
-

SIZE
A3

CAGE CODE
0198G

DRAWING NO
C-1905A0027

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
5

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EC7629-000](#)