



| REVISIONS | | | | | |
|-----------|-----|-------------|------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | — | SEE SHEET 1 | — | — | — |

| DESCRIPTION | PART NO. |
|---------------|-------------|
| STB09-0-0 | 1768039-4 |
| STB09-1-1 | 1768039-6 |
| STB09-2-2 | 1768039-9 |
| STB09-3-3 | 1-1768039-2 |
| STB09-5-5 | 1-1768039-6 |
| STB09-6-6 | 1-1768039-8 |
| STB09-7-7 | 1-1768039-9 |
| STB09-8-8 | 2-1768039-0 |
| STB09-BLANK-0 | 2-1768039-4 |
| STB09-BLANK-1 | 2-1768039-5 |
| STB09-BLANK-2 | 2-1768039-6 |
| STB09-BLANK-3 | 2-1768039-7 |
| STB09-BLANK-5 | 2-1768039-8 |
| STB09-BLANK-6 | 2-1768039-9 |
| STB09-BLANK-7 | 3-1768039-0 |
| STB09-BLANK-8 | 3-1768039-1 |
| STD09W/1-12 | 7-1768710-9 |
| STD09W/SA | 3-1768044-5 |
| STD09W/SAB | 3-1768044-6 |
| STD09W-0 | 808756-000 |
| STD09W-1 | 564314-000 |
| STD09W-2 | 881128-000 |
| STD09W-3 | 451612-000 |
| STD09W-4 | 776688-000 |
| STD09W-5 | 411220-000 |
| STD09W-6 | 062724-000 |
| STD09W-7 | 638470-000 |
| STD09Y-SLASH | 792924-000 |
| STB09-C-2 | 3-1768039-2 |
| STB09-T-2 | 4-1768039-2 |
| STD09W-AC | 3-1768044-8 |
| STD09Y/SA | 5-1768044-7 |





| DESCRIPTION | PART NO. |
|------------------------|------------------------|
| STD09W-8 | 671050-000 |
| STD09W-9 | 519158-000 |
| STD09W-A | 317872-000 |
| STD09W-A-LC | 3-1768044-9 |
| STD09W-B | 929926-000 |
| STD09W-BLANK | 4-1768044-0 |
| STD09W-B-LC | 4-1768044-1 |
| STD09W-C | 595148-000 |
| STD09W-COLON | 950990-000 |
| STD09W-D | 535494-000 |
| STD09W-D-LC | 4-1768044-2 |
| STD09W-DOT | 4-1768044-3 |
| STD09W-E | 318782-000 |
| STD09W-EARTH | 4-1768044-4 |
| STD09W-F | 778086-000 |
| STD09W-G | 362886-000 |
| STD09W-H | 659958-000 |
| STD09W-I | 234392-000 |
| STD09W-J | 429560-000 |
| STD09W-K | 594054-000 |
| STD09W-K-LC | 5-1768044-0 |
| STD09W-L | 591020-000 |
| STD09W-L-LC | 5-1768044-1 |
| STD09W-M | 853188-000 |
| STD09W-MINUS | 5-1768044-2 |
| STD09W-N | 547972-000 |
| STD09W-P | 294582-000 |



OBSOLETE PART

| DESCRIPTION | PART NO. |
|--------------|-------------|
| STD09W-PLUS | 5-1768044-5 |
| STD09W-Q | 702368-000 |
| STD09W-R | 071620-000 |
| STD09W-S | 701134-000 |
| STD09W-SLASH | 190726-000 |
| STD09W-T | 594256-000 |
| STD09W-U | 588548-000 |
| STD09W-V | 651644-000 |
| STD09W-W | 910358-000 |
| STD09W-X | 697154-000 |
| STD09W-Y | 068920-000 |
| STD09W-Z | 952914-000 |
| STD09Y-0 | 047316-000 |
| STD09Y-1 | 064090-000 |
| STD09Y-2 | 700690-000 |
| STD09Y-3 | 410908-000 |
| STD09Y-4 | 422172-000 |
| STD09Y-5 | 131226-000 |
| STD09Y-6 | 746782-000 |
| STD09Y-7 | 007980-000 |
| STD09Y-8 | 634544-000 |
| STD09Y-9 | 645636-000 |
| STD09Y-A | 862816-000 |
| STD09Y-AC | 6-1768044-0 |
| STD09Y-B | 036610-000 |
| STD09Y-BLANK | 6-1768044-2 |
| STD09Y-C | 452642-000 |

| DESCRIPTION | PART NO. |
|--------------|-------------|
| STD09Y-COLON | 6-1768044-4 |
| STD09Y-D | 281690-000 |
| STD09Y-DOT | 6-1768044-6 |
| STD09Y-E | 882530-000 |
| STD09Y-EARTH | 6-1768044-7 |
| STD09Y-F | 017172-000 |
| STD09Y-G | 112902-000 |
| STD09Y-H | 075034-000 |
| STD09Y-I | 769976-000 |
| STD09Y-J | 327448-000 |
| STD09Y-K | 672532-000 |
| STD09Y-L | 509762-000 |
| STD09Y-M | 205508-000 |
| STD09Y-MINUS | 7-1768044-5 |
| STD09Y-N | 667860-000 |
| STD09Y-P | 597516-000 |
| STD09Y-PLUS | 7-1768044-8 |
| STD09Y-Q | 247002-000 |
| STD09Y-R | 920140-000 |
| STD09Y-S | 590022-000 |
| STD09Y-T | 497634-000 |
| STD09Y-U | 491394-000 |
| STD09Y-V | 423154-000 |
| STD09Y-W | 365646-000 |
| STD09Y-X | 523918-000 |
| STD09Y-Y | 362942-000 |
| STD09Y-Z | 322370-000 |

| | | | | | |
|---|--|--|--|---|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 23MAR2013 RAGHAVENDRA K | |  TE Connectivity | |
| | | CHK 23MAR2013 KEAN ALAN | | | |
| DIMENSIONS: mm | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD 23MAR2013 MARIO APPELLO | |
|  | | 0 PLC ± - | | NAME | |
| | | 1 PLC ± - | | SNAP-ON MARKER STB/STD SIZE 09 WITH APPLICATOR | |
| | | 2 PLC ± - | | - | |
| | | 3 PLC ± - | | - | |
| | | 4 PLC ± - | | SIZE | |
| | | ANGLES ± - | | CAGE CODE | |
| MATERIAL | | FINISH | | DRAWING NO | |
| - | | - | | RESTRICTED TO | |
| | | WEIGHT | | - | |
| CUSTOMER DRAWING | | | | SCALE NTS | |
| | | | | SHEET 3 OF 3 | |
| | | | | REV 6 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[STD09W-3](#)