



Introducing T200 Ident Printer

Get the most out of your Cable Identification and Labeling. The new all-in-one T200 Ident printer from TE Connectivity (TE) brings together a complete solution for your economy range of Thermal Transfer printing needs. The increased accuracy and the added flexibility of a movable Media sensor extends the variety of products approved for this printer while reducing the number of misprints. The touch screen provides an easier user interface for setup and enhances your using experience. Reduce cost and any downtime between print jobs with the T200 Ident Printer.

KEY FEATURES

- Light-weight
- Automatic calibration
- Simple ribbon and media loading procedure
- Superior print position accuracy
- Cutter & perforator option available
- Touch screen
- Full DHCP
- LAN connection

APPLICATIONS

- For TE identification marker sleeves, cable markers, and labels
- Ideal Low volume printing

PRINTER DIMENSIONS

- Depth: 322 mm
- Height: 189 mm
- Width: 253 mm
- Weight: 4 kg

ELECTRICAL

- 100 to 240 V
- 50/60 Hz
- FPC

OPERATING CONDITIONS

- 5°C to 40°C (40°F to 104°F)
- 25 to 85% non-condensing RH

PRINTING METHOD

300 dpi Thermal Transfer

PRINTING SPEED

30, 40, 50, 75, 100, 125 mm/s (recommended 50 mm/s)

APPROVALS & DECLARATIONS

CE, FCC Class A, CB, CCC, UL, GOST

The printer's 300dpi resolution combined with recommended media and Thermal Transfer ribbons meet all relevant TE Connectivity RW specifications.

*The T200 Ident Printer is available as a stand-alone solution or as a package with TE's WINTOTAL-5-DONGLE Software.

te.com/products/identification-labeling



PRODUCT PROPERTIES

- Print width max: 108 mm
- Label width: 10 to 116 mm (backing paper width)
- Label Height: 6 to 1,000 mm

INTERFACES

- USB 2.0 (Full Speed)
- LAN 10/100 Base (Ethernet)
- USB master ports on the front and back of the printer

SOFTWARE

- WINTOTAL-5
- PEP-5- (Express, Pro, Suite)

PRODUCT OFFERING

TE Connectivity Printers	
T200-IDENT-PRINTER (Standard printer)	EC6996-000
T200-IDENT-SWARE-PRINTER (Printer and Wintotal-5-dongle-pack)	EC6997-000
Spare Parts	
T200-IDENT-PRINthead	EC8927-000 (300 dpi Print head)
T200-IDENT-DR4-DRIVEROLLER	EC8926-000 (Drive roller)
Accessories	
T200-IDENT-CUTTER	EC8456-000 (Cutter)
T200-IDENT-PERFORATOR	EC8869-000 (Perforator - max. product width of 45 mm)

For further technical details please consult the latest issue of the T200 Ident printer Technical data sheet (TE document TTDS-256)

APPROVED PRODUCT & RIBBON COMBINATIONS

CABLE IDENT

Product Type	Ribbon Type
CM-NMX	1330-3300-10
CM-SCE-TP, D-SCE, D-SCE-FLAT-SP, HLXNEL, HS, HXCT, HX-SCE, TMS-90-SCE, WM-SCE	1966-RIBBON
HTCM-SCE-TP, HT-SCE	TMS-RJS-RIBBON-4HT
Multimark, RPS, TMS-SCE	TMS-RJS-RIBBON-4RPSCE
TTMS, TTMS-2X, TTMS-MP	2000P-RIBBON-4TT (Narrow/Med), TMS-RJS-RIBBON-4RPSCE

LABELS

Product Type	Ribbon Type
CP, HM, HMM, HPK, HW, MP, MV, NC, TN, TTP, WP, WPM, WV	1330-0607-10
EET-P-4, EET-P-8A, EET-P-9, EET-V-9, SET...PSL	TTB-110SC/300
EET-G-4, EET-PY-9, EET-K-9, EET-V-8A, EET-V-4-W, EET-SL...-V-4-W, IKT (PV-4, PY-9), IMT (PV-4, PY-9)	TTB-110SC/360-AQ529
EP	1330-0600-10
KMT	TTB-110SC/300WH
PPT	TTB-114SC/360-AQ529
PVF, TTVF	1330-3300-10
SB Plus	TMS-RJS-RIBBON-4RPSCE
SP	1330-0607-10
T1K, T2K	1330-0619-10

For the approved Ribbon, Printer and Product combination, please consult the latest revision of the Identification Printer Product Ribbon Matrix, document number 411-121005 on te.com

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

te.com/products/identification-labeling



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T200-IDENT-DR4-DRIVEROLLER](#) [T200-IDENT-PRINTHEAD](#) [T200-IDENT-CUTTER](#) [T200-IDENT-PERFORATOR](#)