

Thermal transfer ribbons



RJS-4RPSCE

Tyco Electronics RJS-4RPSCE is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics TMS-SCE, RPS and HL cable markers wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T308S, T3 12M, T3 12Z**, T408M, T6 12M-DS, T3 12S
Compatible materials	TMS-SCE, RPS, SB, HL, HS, HC
<i>**Not available in Europe, Middle East or Africa</i>	

Ordering information

Product order code	TMS-RJS-RIBBON-4RPSCE
Description	Tyco Electronics 4RPSCE thermal transfer ribbon for T308S, T3 12S, T3 12M, T3 12Z**, T408M and T6 12M-DS printers
<i>**Not available in Europe, Middle East or Africa</i>	

101-4RPSCE

Tyco Electronics 101-4RPSCE is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics TMS-SCE, RPS wire marker sleeve products and SB self-laminating labels. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	74 meters (242 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T208M, T2 12M
Compatible materials	TMS-SCE, RPS, SB

Ordering information

Product order code	TMS-101-RIBBON-4RPSCE
Description	Tyco Electronics 4RPSCE thermal transfer ribbon for T208M and T2 12M printers

RJS-4HT

Tyco Electronics RJS-4HT is a high temperature black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HT-SCE high temperature wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T3 12M, T408M, T6 12M-DS
Compatible materials	HT-SCE, HTCM-SCE-TP (T3 12M only)

Ordering information

Product order code	TMS-RJS-RIBBON-4HT
Description	Tyco Electronics 4HT thermal transfer ribbon for T3 12M, T408M and T6 12M-DS printers

Thermal transfer ribbons

101-4HT

Tyco Electronics 101-4HT is a high temperature black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HT-SCE high temperature wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	74 meters (242 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T208M, T212M
Compatible materials	HT-SCE

Ordering information

Product order code	TMS-101-RIBBON-4HT
Description	Tyco Electronics 4HT thermal transfer ribbon for T208M and T212M printers

1910

Tyco Electronics 1910 is a high durability high contrast resin/wax thermal transfer ribbon tested and approved for use on the HLX-zero halogen cable marker tape and the HXTM-FB rail tags. For reliable print performance use with Tyco Electronics recommended printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	210 meters (689 feet)
Ink	Resin/wax
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T408M
Compatible materials	HLX, HXTM-FB
Tyco Electronics	TTDS-080

Ordering information

Product order code	1910-RIBBON-4T300
Description	Tyco Electronics 1910 thermal transfer ribbon for T408M printers

1966 - RIBBON

Tyco Electronics 1966-RIBBON is an ultra-high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HX, HX-SCE and D-SCE wire marker sleeves as well as CM-SCE-TP and HLX cable markers. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Tyco Electronics	TTDS-099
Ribbon width	100 mm (3.9 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printer	T312M
Compatible materials	CM-SCE-TP, D-SCE, HLX, HS, HX, HXTM-FB, HX-SCE, HL

Ordering information

Product order code	1966-RIBBON
Description	Tyco Electronics 1966 thermal transfer ribbon for T312M

T200-RIBBON-1966

Tyco Electronics T200-RIBBON-1966 is an ultra-high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HX-SCE wire marker sleeves. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	100 mm (3.9 inches)
Ribbon length	74 meters (242 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T212M
Compatible materials	HX-SCE, D-SCE, HLX-NEL

Ordering information

Product order code	T200-RIBBON-1966
Description	Tyco Electronics 1966 thermal transfer ribbon for T212M

1330-0606

Tyco Electronics 1330-0606 is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width*	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Wax/Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312M, T312S, T312Z**, T408M
Compatible materials	SB, NC, WP, HW, MP, HM, MV

* Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code	1330-0606-10
Description	Tyco Electronics RHQ thermal transfer ribbon for all T300 and T400 printers

1330-0607

Tyco Electronics 1330-0607 is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width*	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312M, T312S, T312Z**, T408M
Compatible materials	CP, HM, HMM, HPK, HW, MP, MV, NC, PVF, TN, TTP, WP, WV, TP, HLTM, SP

* Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code	1330-0607-10
Description	Tyco Electronics RHD thermal transfer ribbon for all T300 and T400 printers

1330-0607-T200

Tyco Electronics 1330-0607-T200 is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	74 meters (242 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T208M, T212M
Compatible materials	HM, HMM, HW, MP, MV, NC, TN, TTP, WP, WV, HPK

Ordering information

Product order code	1330-0607-T200
Description	Tyco Electronics RHD thermal transfer ribbon for T208M and T212M printers

1330-0619

Tyco Electronics 1330-0619 is a high temperature black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable Kapton® labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width*	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312M, T312S, T312Z**, T408M
Compatible materials	T1K, T2K, TSK, T2Y, KTT

* Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code	1330-0619-10
Description	Tyco Electronics RHT thermal transfer ribbon for all T300 and T400 printers

Thermal transfer ribbons

1330-0600

Tyco Electronics 1330-0600 is a high quality black wax thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable paper labels. See right for compatible material. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width*	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Wax
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312M, T312S, T312Z**, T408M
Compatible materials	EP

* Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code	1330-0600-10
Description	Tyco Electronics RS thermal transfer ribbon for all T300 and T400 printers

1330-0600-T200

Tyco Electronics 1330-0600-T200 is a high quality black wax thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable paper labels. See right for compatible material. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	74 meters (242 feet)
Ink	Wax
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T208M, T212M
Compatible materials	EP

Ordering information

Product order code	1330-0600-T200
Description	Tyco Electronics RS thermal transfer ribbon for T200 printers

3300

Tyco Electronics 3300 is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width*	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	Black
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312S, T312M, T312Z, T408M
Compatible materials	PVF, TTVF

* Available in additional sizes by custom quotation

Ordering information

Product order code	1330-3300-10
Description	Tyco Electronics 3300 thermal transfer ribbon for all T300 and T408M printers

T300-WH

White resin based ribbons are available to print on Tyco Electronics TMS-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	White
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312S, T312Z**, T312M and T-408M
Compatible materials	TMS-SCE (T312M only), CP, TTP

**Not available in Europe, Middle East or Africa

Ordering information

Product order code	T300-RIBBON-WH
Description	Tyco Electronics thermal transfer ribbon for T300 and T400 printers

T200-WH

White resin based ribbons are available to print on Tyco Electronics TMS-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications	
Ribbon width	1 10 mm (4.33 inches)
Ribbon length	70 meters (230 feet)
Ink	Resin
Standard color	White
Ribbon wind direction	Ink side out
Compatible printers	T208M, T2 12M
Compatible materials	TMS-SCE (T2 12M only) HM, MP, MV, TTP
Ordering information	
Product order code	T200-RIBBON-WH
Description	Tyco Electronics thermal transfer white ribbon for T200 printers

T300-WH-4HT

White resin based ribbons are available to print on Tyco Electronics HT-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications	
Ribbon width	1 14 mm (4.49 inches)
Ribbon length	300 meters (984 feet)
Ink	Resin
Standard color	White
Ribbon wind direction	Ink side out
Compatible printers	T3 12M
Compatible materials	HT-SCE
Ordering information	
Product order code	T300-RIBBON-WH-4HT
Description	Tyco Electronics thermal transfer white ribbon for all T308M, T3 12M and T408M printers

T200-WH-4HT

White resin based ribbons are available to print on Tyco Electronics HT-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications	
Ribbon width	1 10 mm (4.33 inches)
Ribbon length	74 meters (242 feet)
Ink	Resin
Standard color	White
Ribbon wind direction	Ink side out
Compatible printers	T2 12M
Compatible materials	HT-SCE
Ordering information	
Product order code	T200-RIBBON-WH-4HT
Description	Tyco Electronics thermal transfer white ribbon for T200 printers

RHCA

RHCA resin based ribbons are specifically designed to print on polyester or metalized polyester Tyco Electronics label products. For print performance and durability use with Tyco Electronics recommended compatible printers. It is not suitable to print on paper or self-laminating products.

General specifications	
Ribbon width	1 10 mm (4.33 inches)
Ribbon length	91 meters (300 feet)
Ink	Resin
Standard color	Red, Blue and Green (see ordering information below)
Ribbon wind direction	Ink side out
Compatible printers	T308S, T3 12M, T3 12S, T3 12Z** and T408M
Compatible materials	CP, HW, HM, HPK, HMM, MP, MV, PVF, WP, WV
<i>**Not available in Europe, Middle East or Africa</i>	
Ordering information	
Product order codes	1330-0620-10 (Red) 1330-0621-10 (Blue) 1330-0622-10 (Green)
Description	Tyco Electronics thermal transfer color ribbon for all T300 and T400 printers

Thermal transfer ribbons

RHCB

RHCB wax-resin based ribbons are specifically designed to print on paper. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width	110 mm (4.33 inches)
Ribbon length	300 meters (9840 feet)
Ink	Wax-Resin
Standard color	Red, Blue and Green (see ordering information below)
Ribbon wind direction	Ink side out
Compatible printers	T308S, T312M, T312S, T312Z** and T408M
Compatible materials	EP

***Not available in Europe, Middle East or Africa*

Ordering information

Product order codes	1330-0630-10 (Red)	1330-0631-10 (Blue)	1330-0632-10 (Green)
Description	Tyco Electronics thermal transfer color ribbon for all T300 and T400 printers		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[C95590-000](#) [557721-000](#) [E45478-000](#) [742412-000](#) [1330-3300-101TT](#) [1330-0607-T200](#) [1330-0607-10](#) [1330-3300-10](#)