



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	REVISED PER ECO-11-010839	25MAY11	RK	HMR
	R	REVISED PER ECO-17-007805	31MAY2017	RS	MM

- 1 PBT.
- 2 LCP.
- 3 TOLERANCE IS $+.007/-0.003$ FOR 6 POSITION AND SMALLER SIZES.
- 4 VOID CORING IN THIS AREA OPTIONAL FOR MOLDING IMPROVEMENT.

<div>2</div>	2.595	2.520	2.400	24	25	2-103653-4
<div>2</div>	2.495	2.420	2.300	23	24	2-103653-3
<div>2</div>	2.395	2.320	2.200	22	23	2-103653-2
<div>2</div>	2.295	2.220	2.100	21	22	2-103653-1
<div>2</div>	2.195	2.120	2.000	20	21	2-103653-0
<div>2</div>	2.095	2.020	1.900	19	20	1-103653-9
<div>2</div>	1.995	1.920	1.800	18	19	1-103653-8
<div>2</div>	1.895	1.820	1.700	17	18	1-103653-7
<div>2</div>	1.795	1.720	1.600	16	17	1-103653-6
<div>2</div>	1.695	1.620	1.500	15	16	1-103653-5
<div>2</div>	1.595	1.520	1.400	14	15	1-103653-4
<div>2</div>	1.495	1.420	1.300	13	14	1-103653-3
<div>2</div>	1.395	1.320	1.200	12	13	1-103653-2
<div>2</div>	1.295	1.220	1.100	11	12	1-103653-1
<div>2</div>	1.195	1.120	1.000	10	11	1-103653-0
<div>2</div>	1.095	1.020	.900	9	10	103653-9
<div>2</div>	.995	.920	.800	8	9	103653-8
<div>2</div>	.895	.820	.700	7	8	103653-7
<div>2</div>	.795	.720	.600	6	7	103653-6
<div>1</div>	.695	.620	.500	5	6	103653-5
<div>1</div>	.595	.520	.400	4	5	103653-4
<div>1</div>	.495	.420	.300	3	4	103653-3
<div>1</div>	.395	.320	.200	2	3	103653-2
<div>1</div>	.295	.220	.100	1	2	103653-1
MATERIAL COLOR-BLACK	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	28JUL00	TE Connectivity		
DIMENSIONS: INCHES		CHK K WRIGHT	28JUL00			
		APVD K WRIGHT	28JUL00	NAME PIN HOUSING, AMPMODU MTE, SINGLE ROW, .100 CL POLARIZED WITH LATCH		
		PRODUCT SPEC 108-25034				
MATERIAL SEE TABLE		APPLICATION SPEC 114-25026		SIZE A2	CAGE CODE 00779	DRAWING NO C=103653
		WEIGHT -		RESTRICTED TO -		
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103653-1](#)