




A

RECOMMENDED HOLE LAYOUT

[illegible]

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

OBSOLETE			64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
			61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
			58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
			56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
			53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
			51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
			48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
			46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
			43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
			41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
			38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
			36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
			33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
			30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
			28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
			25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
			23.37 [.920]	25.27 [.995]	8	9	5-103669-8
			20.83 [.820]	22.73 [.895]	7	8	5-103669-7
			18.29 [.720]	20.19 [.795]	6	7	5-103669-6
			15.75 [.620]	17.65 [.695]	5	6	5-103669-5
			13.21 [.520]	15.11 [.595]	4	5	5-103669-4
			10.67 [.420]	12.57 [.495]	3	4	5-103669-3
			8.13 [.320]	10.03 [.395]	2	3	5-103669-2
			5.59 [.220]	7.49 [.295]	1	2	5-103669-1
	REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY

3-5-91

DWN
M. RIDER

2-14-92

APVD
M. RIDER

2-14-92

NAME

DIMENSIONS:
INCHES

0 PLC ± —

1 PLC ± —

2 PLC ± 0.13[.005]

3 PLC ± —

4 PLC ± —

ANGLES ± —

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC

108-25034

APPLICATION SPEC

114-25026

MATERIAL
HOUSING: LCP,
CONTACTS: BRASS

FINISH
SEE TABLE

WEIGHT

—

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV AC

TE Connectivity

HDR ASSY, VERT, SINGLE ROW

2.54 [.100] C/L 0.64 [.025] SQ POST

WITH PLZN, AMPMODU MTE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

C=103669

—

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103669-3](#)