


RELEASED FOR PUBLICATION

注記：




1. 運用コンタクト : 0-1123721-1
2. 嵌合相手製品型番 : □-1123723-□
□-1123724-□

NOTES:

1. APPLICABLE CONTACT P/N : 0-1123721-1
2. MATING CONN P/N: []-1123723-[]
[]-1123724-[]
3. 7-1123722-[] MEET GWT(GLOW WIRE TEST)
750 DEGREE SPEC




7.50	41.10	43.50	39.60	■ 茶色 (NATURAL)	11	7-1123722-1	
				■ 緑 (GREEN)		6-	-1
				■ 黒 (BLACK)		5-	-1
				■ 赤 (RED)		4-	-1
				■ 青 (BLUE)		3-	-1
				■ 黄 (YELLOW)		2-	-1
	37.14	39.54	35.64	■ 茶色 (NATURAL)	10	7-	-0
				■ 緑 (GREEN)		6-	-0
				■ 黒 (BLACK)		5-	-0
				■ 赤 (RED)		4-	-0
				■ 青 (BLUE)		3-	-0
				■ 黄 (YELLOW)		2-	-0
	33.18	35.58	31.68	■ 茶色 (NATURAL)	9	7-	-9
	D	C	B	A	ハウジング色調 (HOUSING COLOR)	極数 (PO5)	型番 (P/N)
寸法 (DIMENSION)							



断面 A
SECT A

D1	REVISED PER ECR-12-010630	14JUN12	A.Z	F.M
D	REVISED PER ECR-12-006506	11APR12	L.L	F.M
C1	REVISED PER ECO-11-005030	21MAR11	RK	HMR

REVISIONS



MATERIAL
55ナイロン UL94V-0
(66NYLON UL94V-0)

FINISH
仕上

OWN	24 JUN '91
N. YAMASAKI	
CHK	24 JUN '91
M. SHINDO	
APVD	24 JUN '91
M. SHINDO	

PRODUCT SPEC 製品規格	108-5609
APPLICATION SPEC 取付適用規格	—//—
WEIGHT	—//—

CUSTOMER DRAWING



TE Connectivity

3.96mm ピッチエコノミーパワー (EP) コネクタ
プラグハウジング

SIZE	CAGE CODE	DRAWING NO
A3	00779	C- 1123722

SCALE	SHEET	OF	REV
1/8" = 1' - 0"	1	1	D1

参考図面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1123722-2](#)