

LOC	DIST	REVISIONS			DATE	DWN	APVD	
		P	LTR	DESCRIPTION				
AI	—	B	CONTACT PIN MATERIAL AND PLATING CHANGE			10JUL2014	KJK	JK
POS. PER ROW	L±0.5	PART NUMBER						
—	—	—						
2	5.08	—2						
3	7.62	1241880 —3						
4	10.16	—4						
5	12.70	—5						
6	15.24	—6						
7	17.78	—7						
8	20.32	—8						
9	22.86	—9						
10	25.40	1— —0						
11	27.94	1— —1						
12	30.48	1— —2						
13	33.02	1— —3						
14	35.56	1— —4						
15	38.10	1— —5						
16	40.64	1— —6						
17	43.18	1— —7						
18	45.72	1— —8						
19	48.26	1— —9						
20	50.80	2— —0						
21	53.34	2— —1						
22	55.88	2— —2						
23	58.42	2— —3						
24	60.96	2— —4						
25	63.50	2— —5						
26	66.04	2— —6						
27	68.58	2— —7						
28	71.12	2— —8						
29	73.66	2— —9						
30	76.20	3— —0						
31	78.74	3— —1						
32	81.28	3— —2						
33	83.82	3— —3						
34	86.36	3— —4						
35	88.90	3— —5						
36	91.44	3— —6						
37	93.98	3— —7						
38	96.52	3— —8						
39	99.06	3— —9						
40	101.60	4— —0						
41	104.14	4— —1						
42	106.68	4— —2						
43	109.22	4— —3						
44	111.76	4— —4						
45	114.30	4— —5						
46	116.84	4— —6						
47	119.38	4— —7						
48	121.92	4— —8						
49	124.46	4— —9						
50	127.00	5— —0						

△ MATING SIDE: MIN. 0.7µm PdNi + MIN. 0.1µm GOLD FLASH BY AREA "F" OVER 1.27µm NICKEL
SOLDER SIDE: MIN. 2.5µm TIN OVER 1.27µm NICKEL

CONTACT PIN	CuZn	△
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	FINISH/COLOR

DIMENSIONS: MASSENNHEITEN mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN ±0.2

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES / WINKEL ± —

DWN A. Zitz 14-DEC-00
CHK A. Zitz 14-DEC-00
APVD —
PRODUCT SPEC PRODUKTSPEZ. 108-18012
APPLICATION SPEC VERARBEITUNGSSPEZ. —
WEIGHT GEWICHT —

MATERIAL SEE TABLE
FINISH OBERFLAECHE/FARBE SEE TABLE
TE Connectivity
NAME AMPMODU II STACKING PIN HEADER, DUAL ROW
SIZE A4 CAGE CODE 00779 DRAWING NO ZEICHNUNGS-NR. 1241880
RESTRICTED TO NUR FUER —

CUSTOMER DRAWING / KUNDENZEICHNUNG

SCALE MASSSTAB 4:1
SHEET BLATT 1 OF 1
REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1241880-3](#)