



Version A (UNSEALED / ungedichtet)		1-929965-0	1-962969-0	J	CuFe2		>2.5-4.0 FLR	E = 4.3 G = 4.5 D _{br} = 2.4	 H = 5.4 K = 5.6 D = 3.2	4.0mm ² = 2.30 3.0mm ² = 2.05	MQC-Applicator 2-878483-2	734285-3	4	5.5	8.5	
		929965-9	962969-9	J												
		929965-8	962969-8	J	CuNiSi											
		929965-7	962969-7	J												
		929965-4	962969-4	J		CuFe2										
		929965-1	962969-1	J	CuNiSi											
		1-929964-0	1-962968-0	J	CuFe2		>1.0-2.5 FLR	E = 3.6 G = 3.8 D _{br} = 1.7	 H = 4.3 K = 4.5 D = 2.6	2.5mm ² = 1.97 2.0mm ² = 1.82 1.5mm ² = 1.67 1.25mm ² = 1.60	MQC-Applicator 2-878482-2	734285-2	4	5.5	8.5	
		929964-9	962968-9	J												
		929964-8	962968-8	J	CuNiSi											
		929964-7	962968-7	J												
		929964-4	962968-4	J		CuFe2										
		929964-1	962968-1	J	CuNiSi											
		1-929963-0	1-962967-0	L	CuFe2		0.5-1.0 FLR	E = 2.6 G = 2.8 D _{br} = 1.1	 H = 3.2 K = 3.4 D = 1.8	1.0mm ² = 1.45 0.75mm ² = 1.36 0.5mm ² = 1.27	MQC-Applicator 2-878481-2	734285-1	3	4.5	7	
		929963-9	962967-9	L												
		929963-8	962967-8	L	CuNiSi											
		929963-7	962967-7	L												
		929963-4	962967-4	L		CuFe2										
		929963-1	962967-1	L	CuNiSi											
		1-929962-0	1-962966-0	J	CuFe2		0.2-0.4 FLR	E = 2.1 G = 2.1 D _{br} = 0.8	 H = 2.5 K = 2.5 D = 1.4	0.35mm ² = 1.11 0.25mm ² = 1.07 0.2mm ² = 1.05	MQC-Applicator 2-878480-2	734285-1	3	4.5	7	
		929962-9	962966-9	J												
		929962-8	962966-8	J	CuNiSi											
	929962-7	962966-7	J													
	929962-4	962966-4	J	CuFe2												
	929962-1	962966-1	J	CuNiSi												

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[929962-1](#)