







THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity			
		CHK					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
		0 PLC ± -		PRODUCT SPEC		2.0MM PITCH HEADER, DIP, RIGHT ANGLE TYPE	
		1 PLC ± 0.3		—			
		2 PLC ± 0.2		APPLICATION SPEC			
		3 PLC ± 0.1		—			
4 PLC ± -		—		SIZE		CAGE CODE	
ANGLES ± 3°		WEIGHT —		DRAWING NO		RESTRICTED TO	
MATERIAL		FINISH		A3		00779	
SEE SHEET 1.		SEE SHEET 1.		C=1470108		—	
CUSTOMER DRAWING				SCALE —		SHEET 2 of 3	
						REV F5	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG. 2006.



COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR



DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.



LABEL

TUBE

CARTON

NOTES:

1. DIMENSION :

TUBE : L=600, W=10, H=10

SHIPPING CARTON : L=615, W=110, H=100



ANTISTATIC 48-011

1,890	30	4-1470108-6
1,008	16	3-1470108-2
1,008	16	3-1470108-0
1,134	18	2-1470108-8
1,260	20	2-1470108-6
1,260	20	2-1470108-4
1,386	22	2-1470108-2
1,575	25	2-1470108-0
1,764	28	1-1470108-8
1,890	30	1-1470108-6
2,205	35	1-1470108-4
2,520	40	1-1470108-2
2,898	46	1-1470108-0
3,528	56	1470108-8
4,410	70	1470108-6
APQ (PCS/CARTON)	PPQ (PCS/TUBE)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK


APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:

FINISH

MATERIAL

FINISH

FINISH



TE Connectivity

NAME

2.0MM PITCH HEADER, DIP, RIGHT ANGLE TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1470108

SCALE

SHEET

3 of 3

REV F5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1470108-4](#)