

- 1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
 2 OBSOLETE

DO NOT SCALE		DIMENSIONS IN MM.			
PART NUMBER	MATERIAL	FINISH	REELING	LOOSE PIECE REF. ONLY	
154717-1	BRASS	NONE	STANDARD	341001-1	
154717-2	PHOS. BRONZE	NONE	STANDARD	341001-2	
154717-3	BRASS	TIN	STANDARD	341001-3	
154717-4	PHOS. BRONZE	TIN	STANDARD	341001-4	
154717-5	PHOS. BRONZE	NONE	STANDARD	341001-5	
154717-6	BRASS	PRE-TIN	STANDARD	341001-6	
154717-7	PHOS. BRONZE	PRE-TIN	STANDARD	341001-7	
154717-8	PHOS. BRONZE	SILVER	STANDARD	341001-8	
154717-9	BRASS	SILVER	STANDARD	341001-9	
154717-10	OBSOLETE	OBSOLETE	OBSOLETE	---	
1-154717-1	BRASS	NONE	REV. REEL VERSION-1	---	
1-154717-2	PHOS. BRONZE	NONE	REV. REEL VERSION-2	---	
1-154717-3	PHOS. BRONZE	PRE-TIN	STANDARD	---	
1-154717-4	BRASS	TIN	REV. REEL VERSION-3	---	
1-154717-5	PHOS. BRONZE	TIN	REV. REEL VERSION-4	---	
1-154717-6	PHOS. BRONZE	TIN	STANDARD (SPLICE FREE VERSION)	---	

C.A.D. FILE CODE C154717

WIRE RANGE 2.5 TO 4.0mm ²		INSULATION RANGE 3.6 TO 4.3mm DIA.	
CUSTOMER DWG FOR REFERENCE ONLY		RELEASED FOR PUBLICATION ORIGINAL 1974	
A		TOLERANCES UNLESS OTHERWISE STATED DEC ± 0.5 ANGLES ± 1°	
		DR. D.A.BARRATT 27.11.91 CH. D.TERRY APP. D.A.BARRATT 	
NAME POSITIVE LOCK RECEPTACLE			
AR4	REVISED PER ECR-20-005366	13APR2020	SS DL
AR3	ECR-15-007886	17JUN15	NK GH
REV	DESCRIPTION	DATE	DWN APVD
SCALE 4/1	LOC E	SIZE A4	DWG.No. C154717
REV AR4	SHEET 1/1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[154717-3](#)