






SHOWN
1-1564559-1




RETAINER IN PRE LOCKED POSITION
Kontaktsicherung in Vorraststellung



RETAINER IN FINAL LOCKED POSITION
2. Kontaktsicherung in Endraststellung




RETAINER MOVING DIRECTION
2. Kontaktsicherung Verschiebeweg




2.1


CODINGS
2:1




A 1-1564559-1
(BLACK)
1-1564559-4
(YELLOW FOR GM)




B 2-1564559-1
(GREY)
2-1564559-4
(YELLOW FOR GM)



C 3-1564559-1
3-1564559-4
(YELLOW FOR GM)






D 4-1564559-1




Z 5-1564559-1


SHOWN
1-1564559-2




RETAINER IN PRE LOCKED POSITION
Kontaktsicherung in Vorraststellung



RETAINER IN FINAL LOCKED POSITION
2.Kontaktsicherung in Endraststellung




RETAINER MOVING DIRECTION
2.Kontaktsicherung Verschiebeweg




2.1


CODINGS
2:1




A 1-1564559-2
(BLACK)




B 2-1564559-2
(GREY)



C 3-1564559-2



D 4-1564559-2



Z 5-1564559-2

USED MCON 1.2mm LL MALE TERMINALS AND SEALS

TE-PN. TERMINALS	WIRE RANGE	TE-PN. SINGLE WIRE SEAL	TE-PN. BLIND PLUG
2141868	0.08 - 0.22mm ²	967067-2	967056-1
1718758	0.25 - 0.35mm ²	967067-2	
1718760	0.5 - 0.75mm ²	967067-1	
1718762	1mm ²	967067-1	

TERMINAL TE-APPLICATION SPEC.: 114-18464.

TE-SUITABLE FEMALE HSG. PASSENDE BUCHSENGEH.	TE- Bestell-Nr. ORDER-NO.	ASSY REV. CODE	Benennung TITLE	QTY	Benennung Einzelteil TITLE	Werkstoff MATERIAL	Oberflaeche/Farbe SURFACE/COLOUR	Pos. ITEM
5-1564559-2	A	Z	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
4-1564559-2	A	D	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PBT-GF30	schwarz/BLACK	1c
3-1564559-2	A	C	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
2-1670918-2	A	B	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PBT-GF30	schwarz/BLACK	1c
1-1670918-2	A	A	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2

3-1670918-1	3-1564559-4	A	C	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
2-1670918-1	2-1564559-4	A	B	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PBT-GF30	gelb/YELLOW	1
1-1670918-1	1-1564559-4	A	A	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PBT-GF30	gelb/YELLOW	1
	5-1564559-1	A	Z	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
	4-1564559-1	A	D	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PBT-GF30	schwarz/BLACK	1
	3-1564559-1	A	C	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
2-1670918-1	2-1564559-1	A	B	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
1-1670918-1	1-1564559-1	A	A	Stiftgehaeuse 4pol. MALE HOUSING 4POS.	1	Kontaktsicherung RETAINER	PBT-GF30	grau/GREY	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		REV. 07 JUL 2008		REV. 08 JUL 2008	
DIMENSIONS: (mm)		PRODUCT SPEC		APPLICATION SPEC	
0 PLG ±0.5		108-34.177-1		114-18910-1	
2 PLG ±0.5		108-34.177-1		114-18910-1	
4 PLG ±0.5		108-34.177-1		114-18910-1	
MATERIAL		FINISH		WEIGHT	
-		-		6.76g	
CUSTOMER DRAWING		SCALE		SHEET	
-		5:1		1 OF 1	

REGRIND MAX. 25%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1564559-1](#)