


1. COIL TRANSIENT VOLTAGE LIMITED TO ± 45 VOLTS
2. SUITABLE FOR USE ON 50 AMP LOAD TRANSFER APPLICATIONS
3. THIS UNIT MEETS THE MATERIAL



REVIEWS			RELEASED	D-7G6SZ	REV. C
REV.	DESCRIPTION	DATE	APPROVED		
A	INITIAL RELEASE	06/04/10	CB		
B	UPDATED BASE MAIN NOTE, ADDED ITEM 4	06/05/22	CB		
C	P.N. REMOVED ITEM 14 & ITEM 3 WAS -010				
C	07-030310 REMOVED ITEM 10, 11, & 13. ADDED KEYWAY	07/05/29	AH		

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/04/10	CB
B	UPDATED BASE MAIN NOTE, ADDED ITEM 4	06/05/22	CB
C	P.N. REMOVED ITEM 14 & ITEM 3 WAS -010		
C	07-030310 REMOVED ITEM 10, 11, & 13. ADDED KEYWAY	07/05/29	AH

GASKET SEALED, VENTED

3 POT SIDE-STAB E
115/200 VAC 400 HZ
50 AMP

SPDT
28 VDC OR 115 VAC 400 HZ
5 AMP

CONTINUOUS
28 VDC
15 VDC AT 25°C
2.5 - 6.5 VDC AT 25°C
.28 AMP MAX. AT 28 VDC AT 25°C
TYPICAL 20 MS
MAX. 25 MS
TYPICAL 10 MS
MAX. 15 MS

-55°C TO +71°C
50,000 FL. MAX.
25 G'S MAX.
10 G'S SHINE
10 G'S

NOTE:

1. COIL TRANSIENT VOLTAGE LIMITED TO 445 VOLTS
2. SUITABLE FOR USE ON 50 AMP LOAD TRANSFER APPLICATIONS
3. THIS UNIT MEETS THE MATERIAL AND WORKMANSHIP REQUIREMENTS OF MIL-R-6106

E - FAX/PWA					
DETECTOR - MS3470L-10BP					
REAR - LOOK, NO. 10, SPLIT					
CB 06/05/22	TER - 7/16 X 13/64 X .032 FL.				
DA 06/05/22	10-32 X 3/8 X 1/8 HEX				
DA 06/05/22	E - WIRING DIAGRAM				
	ACTOR ASSEMBLY - PRIMARY				
	INIAL SHIELD ASSY				
E - NAME	E - WARNING				
NAME/CALLOUT OR DESCRIPTION	PSOH NO	DRAWING OR SPECIFICATION	MATERIAL OR NOTE		

Tyco Electronics

121 Hotchkiss Division, 175 N. DIAMOND STREET, WARSFIELD, OHIO 44080

CONTACTOR - 3PDT, SIDE-STABLE
50 AMP, 400 HZ, 28 VDC COIL

DWG NO. D-7G6SZ

REF TE P/N 1-1616957-4

093

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1616957-4](#)