

LOC		DIST		REVISIONS					
P	LTR	DESCRIPTION				DATE	DWN	APVD	
	E	UPDATED PART REVISION				12AUG2014	KR	JC	
	F	UPDATED PART REVISION				18AUG2014	KR	JC	
	G	UPDATED DRAWING				19FEB2015	KR	MZ	
	H	ECR-15-009919 AND ECR-15-010559				16JUL2015	RS	JL	

(SEE TABLE 1)

ØE

22.4

7.70

1.60

1.83

GROOVE

ØD

(SEE TABLE 1)

NOTES:

1) PACKAGING: SEE TE PACKAGING SPEC. 107-20294

2) PART NOT YET RELEASED FOR PRODUCTION

ADDITIONAL VIEWS, FOR REFERENCE	3D VIEWS FOR REFERENCE	PART NUMBER
		2-293476-2
		1-293476-2
		293476-2

NOTE	CROSS SECTION (sqmm)	DIMENSION "E"	DIMENSION "D"	NO. OF GROOVES	NET WEIGHT (g)	DESCRIPTION	PART NUMBER
2	4.0	3.9	2.8	0	~0.8	MACHINE PIN CONTACT NECTOR* M-LINE	2-293476-2
	2.5	3.3	2.2	0	~0.7	MACHINE PIN CONTACT NECTOR* M-LINE	1-293476-2
	1.5	3.3	1.7	1	~0.8	MACHINE PIN CONTACT NECTOR* M-LINE	293476-2

DIMENSIONS:		DWN		MATERIAL		FINISH	
mm		M. ZUCCA		BRASS		TIN PLTD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK M. ZUCCA					
0 PLC ±		220CT2009					
1 PLC ±0.3		220CT2009					
2 PLC ±0.20		220CT2009					
3 PLC ±		APVD G. TURCO		NAME			
4 PLC ±		PRODUCT SPEC		MACHINED PIN CONTACT NECTOR* M-LINE			
ANGLES ±3°		APPLICATION SPEC		SIZE			
		114-20152		CAGE CODE			
		WEIGHT		DRAWING NO			
		SEE TABLE 1		RESTRICTED TO			
		Customer Drawing		SCALE			
				3:1			
				SHEET			
				1 OF 1			
				REV			
				H			

2010

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

BY -

COPYRIGHT 2010

©

0 PLC ±

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±

4 PLC ±

ANGLES ±3°



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[293476-2](#)