

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	02APR2020	AY	PS

D

D

C



C

B


B

A

A




- NOTES:
1. MATERIAL:
LCP BLACK, UL94 V0
 2. N = NUMBER OF POSITION PER HOUSING.
 3. HOUSING TO BE USED WITH CRIMP CONTACTS
2316113 (AWG 28-24/0.08-0.22 mm²) AND
2316114 (AWG 30-28/0.05-0.08 mm²)
 4. PACKAGING : BULK BOX




CENTERLINE FOR ODD AND EVEN
POSITION HOUSINGS

SCALE 5:1





DUAL ROW HOUSING
PLAIN VERSION
1- -0 AS SHOWN



SCALE 5:1

BOX PACKAGING		
5-2316108-0	50.1	50
4-2316108-8	48.1	48
4-2316108-6	46.1	46
4-2316108-4	44.1	44
4-2316108-2	42.1	42
4-2316108-0	40.1	40
3-2316108-8	38.1	38
3-2316108-6	36.1	36
3-2316108-4	34.1	34
3-2316108-2	32.1	32
3-2316108-0	30.1	30
2-2316108-8	28.1	28
2-2316108-6	26.1	26
2-2316108-4	24.1	24
2-2316108-2	22.1	22
2-2316108-0	20.1	20
1-2316108-8	18.1	18
1-2316108-6	16.1	16
1-2316108-4	14.1	14
1-2316108-2	12.1	12
1-2316108-0	10.1	10
2316108-8	8.1	8
2316108-6	6.1	6
2316108-4	4.1	4
PART NO.	DIM "E"	N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29OCT2017 RAKSHITH R NAYAK		 TE Connectivity				
DIMENSIONS: mm		CHK 29OCT2017 RAKSHITH R NAYAK						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11DEC2017 PRASHANTH S		NAME AMPMODU 2mm RECEPTACLE, wTB HOUSING, CRIMP, DUAL ROW, PLAIN -			
			PRODUCT SPEC 108-64040-1					
	0 PLC ±-		APPLICATION SPEC 114-32173		SIZE A2	CAGE CODE 00779	DRAWING NO C=2316108	RESTRICTED TO -
	1 PLC ±0.15		WEIGHT -					
	2 PLC ±0.10							
	3 PLC ±-							
4 PLC ±-								
MATERIAL SEE NOTE 1 -		ANGLES FINISH ±2° - -						
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2316108-0](#)