

© -TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AF	ECO-20-004897	24AUG2020	SB	JB

1

2

3

4

.38±.020

PIN 1 IDENT DOT

DATE CODE

435469-3

AMP

XXXX

.022±.002

.100 TYP.

A±.02

.36±.020 TYP.

.14±.020

.012 TYP.

.19±.010

.315±.010

.02^{+.01}_{-.00}

STANDOFF, 4 PLC.

.29±.020 TYP.

ACTUATOR

MOUNTING SURFACE

.120±.010 TYP.

.050±.010 TYP.

.46±.020

ACTUATOR

FIGURE 1
LEVER ACTUATOR SHOWN

1

2

FIGURE 2

DPST

4PST

CONTACT ARRANGEMENT

1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7519.

2. SWITCH SHOWN IN OPEN POSITION.

3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLACK.

4. LASER MARK WILL VARY ON 2 POSITION SIDES DUE TO SPACE RESTRICTIONS.

5. .315 DIMENSION APPLIES AT TERMINAL TIPS.
TERMINALS ARE .300^{+.010}-.000 AT MOUNTING SURFACE.

6. ACTUATOR COLOR IS BLUE.

7. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

9. MARKS WILL BE ADDED BY LASER MARK PROCESS.

7	8	OBSOLETE	AS SHOWN	NONE	.28	DPST	2	8-435469-4
	7		FIG 1	NONE	.48	4PST	4	8-435469-1
			- FIG 1	AS SHOWN	1.28	DPST	12	7-435469-6
			- FIG 1	AS SHOWN	1.08	DPST	10	7-435469-5
			- FIG 1	AS SHOWN	.88	DPST	8	7-435469-4
			- FIG 1	AS SHOWN	.68	DPST	6	7-435469-3
			- FIG 1	AS SHOWN	.48	DPST	4	7-435469-2
			- FIG 1	NONE	.28	DPST	2	7-435469-1
			AS SHOWN	NONE	.28	DPST	2	5-435469-9
			AS SHOWN	NONE	.48	4PST	4	5-435469-7
			AS SHOWN	AS SHOWN	.88	DPST	8	5-435469-3
8	7	OBSOLETE	AS SHOWN	NONE	.28	DPST	2	3-435469-4
			FIG 1	FIG 2	.88	4PST	8	3-435469-2
			FIG 1	NONE	.48	4PST	4	3-435469-1
			- FIG 1	AS SHOWN	1.28	DPST	12	2-435469-6
			- FIG 1	AS SHOWN	1.08	DPST	10	2-435469-5
			- FIG 1	AS SHOWN	.88	DPST	8	2-435469-4
			- FIG 1	AS SHOWN	.68	DPST	6	2-435469-3
			- FIG 1	AS SHOWN	.48	DPST	4	2-435469-2
			- FIG 1	NONE	.28	DPST	2	2-435469-1
		SUPERSEDED BY 2-435469-6	AS SHOWN	AS SHOWN	1.28	DPST	12	1-435469-0
8		OBSOLETE	AS SHOWN	NONE	.28	DPST	2	435469-9
			AS SHOWN	NONE	.48	4PST	4	435469-7
			AS SHOWN	FIG 2	.88	4PST	8	435469-6
			AS SHOWN	AS SHOWN	1.08	DPST	10	435469-4
8		OBSOLETE	AS SHOWN	AS SHOWN	.88	DPST	8	435469-3
			AS SHOWN	AS SHOWN	.68	DPST	6	435469-2
			AS SHOWN	AS SHOWN	.48	DPST	4	435469-1
			ACTUATOR	TOP MARKING	A	SWITCH TYPE	NO OF POSN.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TALLEY 3-15-90	TE Connectivity		
CHK R.MILLER 3-27-90		NAME			
APVD H.LEITER 3-27-90		PRODUCT SPEC		SWITCH ASSY, DIP, TYPE C, 7000 SERIES, DPST & 4PST	
APPLICATION SPEC		-		-	
WEIGHT		-		SCALE	
CUSTOMER DRAWING		A2		00779	

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=435469	-
SCALE		SHEET	REV
4:1		1 OF 1	AF

1471-9 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-435469-1](#)