



	6-	↑	-2	↑	130	64	81.28	89.62	91.25	93.90
	6-		-1		120	59	74.93	83.27	84.90	87.55
	6-		-0		100	49	62.23	70.57	72.20	74.85
	5-		-9		80	39	49.53	57.87	59.50	62.15
	5-		-8		68	33	41.91	50.25	51.88	54.53
	5-		-7		60	29	36.83	45.17	46.80	49.45
	5-		-6		50	24	30.48	38.82	40.45	43.10
	5-		-5		40	19	24.13	32.47	34.10	36.75
OBSOLETE	5-		-3		30	14	17.78	26.12	27.75	30.40
	5-		-1	0.00076	20	9	11.43	19.77	21.40	24.05
OBSOLETE	4-		-2	↑	130	64	81.28	89.62	91.25	93.90
OBSOLETE	4-		-1		120	59	74.93	83.27	84.90	87.55
	4-		-0		100	49	62.23	70.57	72.20	74.85
	3-		-9		80	39	49.53	57.87	59.50	62.15
	3-		-8		68	33	41.91	50.25	51.88	54.53
	3-		-7		60	29	36.83	45.17	46.80	49.45
	3-		-6		50	24	30.48	38.82	40.45	43.10
OBSOLETE	3-		-5		40	19	24.13	32.47	34.10	36.75
	3-		-3		30	14	17.78	26.12	27.75	30.40
	3-		-1	0.0005	20	9	11.43	19.77	21.40	24.05
OBSOLETE	1-		-2	↑	130	64	81.28	89.62	91.25	93.90
	1-		-1		120	59	74.93	83.27	84.90	87.55
	1-		-0		100	49	62.23	70.57	72.20	74.85
			-9		80	39	49.53	57.87	59.50	62.15
OBSOLETE			-8		68	33	41.91	50.25	51.88	54.53
			-7		60	29	36.83	45.17	46.80	49.45
			-6		50	24	30.48	38.82	40.45	43.10
			-5		40	19	24.13	32.47	34.10	36.75
			-3		30	14	17.78	26.12	27.75	30.40
	5175473-1			0.0002	20	9	11.43	19.77	21.40	24.05
	PART NO.			Au PLATE	POS.	n	A	B	C	D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Julyee Zhu 19AUG2004 CHK Steven Yao 19AUG2004 APVD Ikuo Enomoto 19AUG2004		 TE Connectivity Ltd.	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC - 2 PLC - 3 PLC - 4 PLC ± ANGLES ± - FINISH		NAME AMP CHAMP .050 CONNECTOR (B-T-B) PLUG CONNECTOR (VERTICAL WITH RETENTION LEG)	
MATERIAL 		WEIGHT 0.000000		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-5175473	RESTRICTED TO
				SCALE NTS	SHEET 1 of 1
				REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-5175473-5](#)