



REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
B7		STATUS CHANGED TO ACTIVE	03JAN2019	SD	PS

- 1 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 OBSOLETE PART NUMBER
- 4 HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK. POST: PHOSPHOR BRONZE.
- 5 .000030 MIN GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 6 .000030 MIN GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 7 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



8	OBSOLETE	6	2	NONE	-	.106	.332	.200	2	6	5-147432-4
8	OBSOLETE	6	2	2	-	.206	.532	.400	4	10	5-147432-1
8	OBSOLETE	5	5	NONE	1.106	.106	1.332	1.200	12	26	147432-3
8	OBSOLETE	5	NONE	4	1.306	.106	1.532	1.400	14	30	147432-2
8	OBSOLETE	5	2	2	-	.206	.532	.400	4	10	147432-1

PLATING	ROW N	ROW M	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DMN: HAYMAKER 14MAR00
 CHK: J. GESFORD 14MAR00
 APVD: J. GESFORD 14MAR00

NAME: HDR ASSY, MOD II, SHRD
 PRODUCT SPEC: 4 SIDES, DR, .100X.100
 APPLICATION SPEC: RA, W/ .025 SQ POSTS, SELECT LOADS

SIZE: A1
 CAGE CODE: 00779
 DRAWING NO: 147432
 WEIGHT: -

CUSTOMER DRAWING SCALE: 4:1 SHEET: 1 OF 1 REV: B7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[147432-3](#) [147432-2](#)