






SHOWN

1-1703498-1




CODINGS
2:1


A
1-1703498-1




B
2-1703498-1




C
3-1703498-1



Z
4-1703498-1




RETAINER IN PRE LOCKED POSITION
2. Kontaktsicherung in Vorraststellung







RETAINER MOVING DIRECTION
2. Kontaktsicherung Verschiebeweg

RETAINER IN FINAL LOCKED POSITION
2. Kontaktsicherung in Endraststellung




SHOWN

1-1703498-2




CODINGS
2:1


A
1-1703498-2
1-1703498-5 (VW)




B
2-1703498-2



C
3-1703498-2







Z
4-1703498-2



USED MCON 1.2mm LL MALE TERMINALS AND SEALS			
TE-PN TERMINALS	WIRE RANGE	TE-PN SINGLE WIRE SEAL	TE-PN BLIND PLUG
2141868	0.08 - 0.22mm ²	967067-2	967056-1
1718758	0.25 - 0.35mm ²	967067-2	
1718760	0.5 - 0.75mm ²	967067-1	
1718762	1mm ²	967067-1	
TERMINAL TE-APPLICATION SPEC.: 114-18464			


SHOWN

1-1703498-3




CODINGS
2:1


A
1-1703498-3
(BLACK)
1-1703498-4
(YELLOW)





B
2-1703498-3
(GREY) (C6)
2-1703498-4
(YELLOW)



C
3-1703498-3



Z
4-1703498-3



2-1670916-1	C	2-1703498-4	B	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
1-1670916-1	C	1-1703498-4	A	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	PBT-GF30	gelb/YELLOW	1b
-	C	4-1703498-3	Z	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
-	C	3-1703498-3	C	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
2-1670916-1	C	2-1703498-3	B	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
1-1670916-1	C	1-1703498-3	A	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
TE SUITABLE FEMALE HSG. PASSENDE BUCHSENGEH.	ASSY REV.	TE Bestell-Nr. ORDER-NO.	CODE	Benennung TITLE	QTY	Benennung Einzelteil TITLE	Werkstoff MATERIAL	Oberflaeche/Farbe SURFACE/C OLOUR	Pos. ITEM

-	C	1-1703498-5	A	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
-	C	4-1703498-2	Z	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
-	C	3-1703498-2	C	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
2-1670916-1	C	2-1703498-2	B	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
1-1670916-1	C	1-1703498-2	A	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
TE SUITABLE FEMALE HSG. PASSENDE BUCHSENGEH.	ASSY REV.	TE Bestell-Nr. ORDER-NO.	CODE	Benennung TITLE	QTY	Benennung Einzelteil TITLE	Werkstoff MATERIAL	Oberflaeche/Farbe SURFACE/C OLOUR	Pos. ITEM

-	C	4-1703498-1	Z	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
-	C	3-1703498-1	C	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
2-1670916-1	C	2-1703498-1	B	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
1-1670916-1	C	1-1703498-1	A	Stiftgehaeuse 2pol. MALE HOUSING 2POS.	1	Kontaktsicherung RETAINER	PA66-GF35	violett/VIOLET	2
TE SUITABLE FEMALE HSG. PASSENDE BUCHSENGEH.	ASSY REV.	TE Bestell-Nr. ORDER-NO.	CODE	Benennung TITLE	QTY	Benennung Einzelteil TITLE	Werkstoff MATERIAL	Oberflaeche/Farbe SURFACE/C OLOUR	Pos. ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.				DATE 19JUN2007			
DIMENSIONS: (mm)				DATE 19JUN2007			
MATERIAL: -				DATE 19JUN2007			
FINISH: -				DATE 19JUN2007			
WEIGHT: 4.48g				DATE 19JUN2007			
CUSTOMER DRAWING				DATE 19JUN2007			

REGRIND MAX. 25%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1703498-3](#)