



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± .-
1 PLC	± .-
2 PLC	± .-
3 PLC	± 0.13[.005]
4 PLC	± .-
ANGLES	± .-
FINISH	

1

2

DWN B. CRISAMORE/DJI
CHK S. BOLASH
APVD M. WALMSLEY

OSJUN05
OSJUN05
OSJUN05

NAME
Tyco Electronics Corporation
Harrisburg, PA 17105-3608
HEADER ASSEMBLY, LONG EJECT LATCHES, RIGHT ANGLE, LOW PROFILE, IDC
-
SIZE CAGE CODE DRAWING NO
A1 00779 1761690
RESTRICTED TO

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV B

	78.74 [3.100]	31	86.36 [3.400]	100.33 [3.950]	64	1-1761690-7
	73.66 [2.900]	29	81.28 [3.200]	95.25 [3.750]	60	1-1761690-6
OBSOLETE	60.96 [2.400]	24	68.58 [2.700]	82.55 [3.250]	50	1-1761690-5
OBSOLETE	48.26 [1.900]	19	55.88 [2.200]	69.85 [2.750]	40	1-1761690-3
OBSOLETE	40.64 [1.600]	16	48.26 [1.900]	62.23 [2.450]	34	1-1761690-1
	35.56 [1.400]	14	43.18 [1.700]	57.15 [2.250]	30	1-1761690-0
	30.48 [1.200]	12	38.10 [1.500]	52.07 [2.050]	26	1761690-9
	27.94 [1.100]	11	35.56 [1.400]	49.53 [1.950]	24	1761690-8
OBSOLETE	22.86 [.900]	9	30.48 [1.200]	44.45 [1.750]	20	1761690-7
	17.78 [.700]	7	25.40 [1.000]	39.37 [1.550]	16	1761690-6
OBSOLETE	15.24 [.600]	6	22.86 [.900]	36.83 [1.450]	14	1761690-5
	12.70 [.500]	5	20.32 [.800]	34.29 [1.350]	12	1761690-4
OBSOLETE	10.16 [.400]	4	17.78 [.700]	31.75 [1.250]	10	1761690-3
OBSOLETE	10.16 [.300]	3	15.24 [.600]	29.21 [1.150]	8	1761690-2
	D	C	B	A	NO OF POS	PART NUMBER

4805 (1/08)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1761690-6](#)