



REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
C		REVISED PER ECO-20-001912	04JUN2020	SB	JO

1. PACKAGE: TUBES
2. MATERIAL: HOUSING- HIGH TEMPERATURE LCP, COLOR - BLACK, CONTACTS- BRASS
3. FINISH: CONTACTS: 0.00254[.0001] BRIGHT TIN-LEAD OVER 0.00127[.00005] NICKEL
4. CIRCUIT POSITION #1 IDENTIFICATION MARK
5. DATUMS ARE ESTABLISHED BY CUSTOMER
6. FINISH: CONTACTS: 0.00254[.0001] MATTE TIN OVER 0.00127[.00005] NICKEL
7. PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
8. 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

6	19	51.31[2.020]	53.21[2.095]	48.26[1.900]	20	5-1825573-3
6	17	48.77[1.920]	50.67[1.995]	45.72[1.800]	19	5-1825573-2
3	19	51.31[2.020]	53.21[2.095]	48.26[1.900]	20	1825573-3
3	17	48.77[1.920]	50.67[1.995]	45.72[1.800]	19	1825573-2
3	10	28.45[1.120]	30.35[1.195]	24.50[1.000]	11	1825573-1
FINISH		POST NO. OMITTED	H	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	06MAR2006	<b>TE</b> TE Connectivity		
		CHK J GESFORD	06MAR2006			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	AMPMODU MTE SURFACE MOUNT, VERTICAL HEADER ASSEMBLY	
		0 PLC	± -	PRODUCT SPEC	108-25034-2	
		1 PLC	± -	APPLICATION SPEC	114-25026	
		2 PLC	± 0.13 [.005]	SIZE	A1	
		3 PLC	± -	CAGE CODE	00779	
MATERIAL		FINISH	SEE TABLE	WEIGHT	1825573	
2		CUSTOMER DRAWING		SCALE	8:1	SHEET 1 OF 1 REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1825573-3](#)