



OBSOLETE	78.74 [3.100]	31	86.36 [3.400]	100.33 [3.950]	64	1-1761685-7	
	73.66 [2.900]	29	81.28 [3.200]	95.25 [3.750]	60	1-1761685-6	
	60.96 [2.400]	24	68.58 [2.700]	82.55 [3.250]	50	1-1761685-5	
	53.34 [2.100]	21	60.96 [2.400]	74.93 [2.950]	44	1-1761685-4	
	48.26 [1.900]	19	55.88 [2.200]	69.85 [2.750]	40	1-1761685-3	
OBSOLETE	43.18 [1.700]	17	50.80 [2.000]	64.77 [2.550]	36	1-1761685-2	
	40.64 [1.600]	16	48.26 [1.900]	62.23 [2.450]	34	1-1761685-1	
	35.56 [1.400]	14	43.18 [1.700]	57.15 [2.250]	30	1-1761685-0	
	30.48 [1.200]	12	38.10 [1.500]	52.07 [2.050]	26	1761685-9	
	27.94 [1.100]	11	35.56 [1.400]	49.53 [1.950]	24	1761685-8	
	22.86 [.900]	9	30.48 [1.200]	44.45 [1.750]	20	1761685-7	
	17.78 [.700]	7	25.40 [1.000]	39.37 [1.550]	16	1761685-6	
	OBSOLETE	15.24 [.600]	6	22.86 [.900]	36.83 [1.450]	14	1761685-5
		12.70 [.500]	5	20.32 [.800]	34.29 [1.350]	12	1761685-4
10.16 [.400]		4	17.78 [.700]	31.75 [1.250]	10	1761685-3	
D		C	B	A	NO OF POS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.						OWN D. CRISAMORE/DIT		OSUNDS		Tyco Electronics Corporation	
						COW S.BOLASH		OSUNDS		Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APPROV'D <b>M.WALMSLEY</b>		NAME		HEADER ASSEMBLY, SHORT EJECT LATCH, VERTICAL, LOW PROFILE, IDC	
		1 PLC ± — 2 PLC ± — 3 PLC ± 0.13[.005] 4 PLC ± —				PRODUCT SPEC —		APPLICATION SPEC		SIZE	
MATERIAL 		FINISH 				WEIGHT —		A1 00779 C=1761685		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 1		REV C	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1761685-3](#)