

4		3		2		1				
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION				REVISIONS				
© COPYRIGHT — TE Connectivity Ltd.		ALL RIGHTS RESERVED.								
				P		LTR	DESCRIPTION	DATE	DWN	APVD
				1		INITIAL CUSTOMER DRAWING		04JUN2018	AFK	LS

VIEW A:
LAYING DIAGRAM

PITCH

101.60 ±1

1

2

LABEL HEIGHT

LABEL LENGTH

MATERIAL LIST

1. PAPER CARRIER - WHITE

2. CABLE LABEL

PRODUCT CODE	PRODUCT PITCH	No. HOLES	LABEL LENGTH	PRINTABLE LENGTH	LABEL HEIGHT
HL104**TS025	12.7 (1/2")	4	45	25	10.4
HL104**TS033	12.7 (1/2")	4	53	33	10.4
HL104**TS038	12.7 (1/2")	4	58	38	10.4
HL104**TS050	12.7 (1/2")	4	70	50	10.4
HL104**TS070	12.7 (1/2")	4	90	70	10.4
HL150**TS025	25.4 (1")	4	45	25	15.0
HL150**TS033	25.4 (1")	4	53	33	15.0
HL150**TS038	25.4 (1")	4	58	38	15.0
HL150**TS050	25.4 (1")	4	70	50	15.0
HL150**TS070	25.4 (1")	4	90	70	15.0
HL203**TS025	25.4 (1")	4	45	25	20.3
HL203**TS033	25.4 (1")	4	53	33	20.3
HL203**TS038	25.4 (1")	4	58	38	20.3
HL203**TS050	25.4 (1")	4	70	50	20.3
HL203**TS070	25.4 (1")	4	90	70	20.3
HL253**TS025	50.8 (2")	4	45	25	25.3
HL253**TS033	50.8 (2")	4	53	33	25.3
HL253**TS038	50.8 (2")	4	58	38	25.3
HL253**TS050	50.8 (2")	4	70	50	25.3
HL253**TS070	50.8 (2")	4	90	70	25.3

NOTES:-

1. NO ACCUMULATIVE ERROR THROUGH PACK IS ACCEPTABLE

2. PACKAGING AS REQUIRED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK 04JUN2018		TE TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± 0.5		PRODUCT SPEC			
		1 PLC ± 0.5		APPLICATION SPEC			
		2 PLC ± -		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
3 PLC ± -		4 PLC ± -		A300779C-1905A0025			
4 PLC ± -		ANGLES ± -		SCALE SHEET 1 OF 1 REV 1			
FINISH		FINISH		CUSTOMER DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EC7552-000](#)