

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL CUSTOMER DRAWING	04JUN2018	AFK	LS

PRODUCT CODE	PRODUCT PITCH	No. HOLES	LABEL LENGTH	PRINTABLE LENGTH	LABEL HEIGHT
HL104**TS025	12.7 (1/2")	4	45	25	10.4
HL104**TS033	12.7 (1/2")	4	53	33	10.4
HL104**TS038	12.7 (1/2")	4	58	38	10.4
HL104**TS050	12.7 (1/2")	4	70	50	10.4
HL104**TS070	12.7 (1/2")	4	90	70	10.4
HL150**TS025	25.4 (1")	4	45	25	15.0
HL150**TS033	25.4 (1")	4	53	33	15.0
HL150**TS038	25.4 (1")	4	58	38	15.0
HL150**TS050	25.4 (1")	4	70	50	15.0
HL150**TS070	25.4 (1")	4	90	70	15.0
HL203**TS025	25.4 (1")	4	45	25	20.3
HL203**TS033	25.4 (1")	4	53	33	20.3
HL203**TS038	25.4 (1")	4	58	38	20.3
HL203**TS050	25.4 (1")	4	70	50	20.3
HL203**TS070	25.4 (1")	4	90	70	20.3
HL253**TS025	50.8 (2")	4	45	25	25.3
HL253**TS033	50.8 (2")	4	53	33	25.3
HL253**TS038	50.8 (2")	4	58	38	25.3
HL253**TS050	50.8 (2")	4	70	50	25.3
HL253**TS070	50.8 (2")	4	90	70	25.3

VIEW A:
LAYING DIAGRAM

MATERIAL LIST

1. PAPER CARRIER - WHITE

2. CABLE LABEL

NOTES:-

1. NO ACCUMULATIVE ERROR THROUGH PACK IS ACCEPTABLE

2. PACKAGING AS REQUIRED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK	04JUN2018		<div><div>TE</div>TE Connectivity</div>				
DIMENSIONS: mm		CHK —	APVD —						NAME
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.5 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —		PRE TAPED THERMAL TRANSFER CABLE LABEL ASSEMBLY			
				APPLICATION SPEC —					
MATERIAL —		FINISH —		WEIGHT — — —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1905A0025	RESTRICTED TO —
CUSTOMER DRAWING				SCALE — — —		SHEET 1 OF 1		REV 1	

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EE0111-000](#)