

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

4

3

2

1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-15-008603	24JUN2015	KG	DW
	C1	ECR-19-015389	21OCT2019	LN	DW
	C2	ECO-20-009383	14JUL2020	LN	DW

BOOT

MAT'L: EPDM RUBBER

EXTENSION

MAT'L: SEE TABLE

SEAL

MAT'L: FLUOROSILICONE RUBBER

CRIMP SUPPORT

MAT'L: NICKEL-SILVER ALLOY

WASHER

MAT'L: STAINLESS STEEL

CRIMP SLEEVE

MAT'L: NICKEL-SILVER ALLOY

1. PACKAGED LOOSE PIECE.

2. DIMENSIONS ARE FOR REFERENCE ONLY.

△3 FOR USE WITH Ø7.5mm BREAKOUT CABLE WITH Ø2.15mm MAXIMUM JACKETED SUBUNITS.

RAL 4004 CLARET VIOLET	ALUMINUM ALLOY	5.7mm	2-1918931-0
RAL 3003 RUBY RED	ALUMINIUM ALLOY	6.2mm	1-1918931-8
BLACK	NICKEL ALUMINUM BRONZE	△3 7.5mm	1-1918931-6
		6.7mm	1-1918931-5
		6.0mm	1-1918931-4
		5.5mm	1-1918931-3
		5.0mm	1-1918931-2
		4.2mm	1-1918931-1
		3.6mm	1-1918931-0
		3.2mm	1918931-9
	ALUMINUM ALLOY	△3 7.5mm	1918931-8
		6.7mm	1918931-7
		6.0mm	1918931-6
		5.5mm	1918931-5
		5.0mm	1918931-4
		4.2mm	1918931-3
		3.6mm	1918931-2
		3.2mm	1918931-1
BOOT COLOR	EXTENSION MATERIAL	MAXIMUM CABLE DIAMETER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

27OCT2006

CHK

K. GLATFELTER

APVD

02JUN2008

D. WERTMAN

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

Customer Drawing

TE Connectivity

CABLE ADAPTER KIT, PLUG,
PRO BEAM JR.

SIZE

A200779

CAGE CODE

C-1918931

DRAWING NO

-

RESTRICTED TO

-

SCALE

3:1

SHEET

1

OF

1

REV

C2

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1918931-7](#)