

Thermofit® Molded Parts

Specification Control Drawing

Part Number: 202B521 thru 598
Description: Boot, Connector Protector

Notes:

1. All dimensions are in $\frac{\text{Inches}}$
[Millimeters]
2. Dimensions appearing in table are as follows:
a - as supplied
b - after unrestricted recovery
3. Part number 202B521 does not have bulb section.





Table of Dimensions

Part Number	H		J		K		P	R	S	KO	KW
	Min a	± 5% b	Min a	Max b	Min a	Max b	± 10% b	± 10% b	± 10% b	± 10% b	± 20% b
202B521	.99 [25,1]	.99 [25,1]	See Note Three		.99 [25,1]	.22 [5,6]	3.26 [82,8]	See Note Three	2.00 [50,8]	.83 [21,1]	.07 [1,78]
202B532	1.12 [28,4]	1.12 [28,4]	1.12 [28,4]	.72 [18,3]	1.12 [28,4]	.26 [6,6]	4.16 [105,7]	2.90 [73,7]	2.37 [60,2]	.66 [16,8]	.07 [1,78]
202B542	1.26 [32,0]	1.26 [32,0]	1.26 [32,0]	.87 [22,1]	1.26 [32,0]	.28 [7,1]	4.63 [117,6]	3.22 [81,8]	2.37 [60,2]	.70 [17,8]	.08 [2,03]
202B553	1.44 [36,6]	1.44 [36,6]	1.44 [36,6]	1.06 [26,9]	1.44 [36,6]	.33 [8,4]	5.81 [147,6]	3.92 [99,6]	3.09 [78,5]	1.06 [26,9]	.08 [2,03]
202B563	1.69 [42,9]	1.69 [42,9]	1.69 [42,9]	1.33 [33,8]	1.69 [42,9]	.39 [9,9]	6.80 [172,7]	4.66 [118,4]	3.09 [78,5]	1.11 [28,2]	.08 [2,03]
202B574	2.03 [51,6]	2.03 [51,6]	2.03 [51,6]	1.67 [42,4]	2.03 [51,6]	.62 [15,7]	7.96 [202,2]	5.02 [127,5]	3.46 [87,9]	1.66 [42,2]	.09 [2,29]
202B585	2.57 [65,3]	2.57 [65,3]	2.57 [65,3]	2.09 [53,1]	2.57 [65,3]	.80 [20,3]	9.74 [247,4]	6.07 [154,2]	3.46 [87,9]	2.18 [55,4]	.10 [2,54]
202B596	2.82 [71,6]	2.82 [71,6]	2.82 [71,6]	2.61 [66,3]	2.82 [71,6]	1.05 [26,7]	11.84 [300,7]	7.40 [188,0]	4.19 [106,4]	2.70 [68,6]	.11 [2,79]
202B598	3.50 [88,9]	3.50 [88,9]	3.42 [88,9]	2.61 [66,3]	3.42 [88,9]	1.05 [26,7]	11.84 [300,7]	7.40 [188,0]	4.19 [106,4]	2.70 [68,6]	.11 [2,79]

Raychem

Raychem Corporation
300 Constitution Drive
Menlo Park, California 94025
415) 361 6055

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Revision: **L**
Date: **8-1-85**

Part Number: 202B521 thru 598
Description: Boot, Connector Protector

Thermofit® Molded Parts Specification Control Drawing

Part Number: 202B521 thru 598
Description: Boot, Connector
Protector

Compatability Chart

Material Dash No.	Material Description	RT Spec	Coating Slash No.	Coating S No.	Coating Description
- 3	Polyolefin, Semi-Rigid	RT-301	N/A		
- 4	Polyolefin, Flexible	RT-1304	N/A		
- 6	Silicone, Flame Retarded	RT-602	N/A		
- 25	Elastomer, Fluid Resistant	RT-1325	N/A		

Ordering Information:

202B5XX — XX — XX / XXX

Base part number _____
Material dash number _____
(see compatability chart)
Modification number _____
(if necessary, see front of SCD binder
for a complete modification list)
Adhesive slash number _____
(if necessary, see compatability chart)

If this document is printed it becomes uncontrolled.
Check for the latest revision.

This drawing is subject to change without notice; consult your nearest field representative for current revision.

Raychem

Raychem Corporation
300 Constitution Drive
Menlo Park, California 94025
415) 361 6055

Revision: **L**
Date: **8-1-85**

Part Number: 202B521 thru 598
Description: Boot, Connector Protector

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[435130-000](#)