





2						7											
LOC		DIST		REVISIONS													
AD		00		P			LTR		DESCRIPTION		DATE		OWN		APVD		
							C		REVISED PER ECO-11-025276			22DEC11		KH		DY	

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A. SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.



LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD	
				-	-	SEE SHEET 1	-	-	-	

	H	5.5	8-2007781-6
	H	4.9	8-2007781-5
	H	4.5	8-2007781-4
	H	5.5	8-2007781-3
	H	4.9	8-2007781-2
	H	4.5	8-2007781-1
	G	5.5	7-2007781-6
	G	4.9	7-2007781-5
	G	4.5	7-2007781-4
	G	5.5	7-2007781-3
	G	4.9	7-2007781-2
	G	4.5	7-2007781-1
	F	5.5	6-2007781-6
	F	4.9	6-2007781-5
	F	4.5	6-2007781-4
	F	5.5	6-2007781-3
	F	4.9	6-2007781-2
	F	4.5	6-2007781-1
	E	5.5	5-2007781-6
	E	4.9	5-2007781-5
	E	4.5	5-2007781-4
	E	5.5	5-2007781-3
	E	4.9	5-2007781-2
	E	4.5	5-2007781-1
	D	5.5	4-2007781-6
	D	4.9	4-2007781-5
	D	4.5	4-2007781-4
	D	5.5	4-2007781-3
	D	4.9	4-2007781-2
	D	4.5	4-2007781-1
	C	5.5	3-2007781-6
	C	4.9	3-2007781-5
	C	4.5	3-2007781-4
	C	5.5	3-2007781-3
	C	4.9	3-2007781-2
	C	4.5	3-2007781-1
	B	5.5	2-2007781-6
	B	4.9	2-2007781-5
	B	4.5	2-2007781-4
	B	5.5	2-2007781-3
	B	4.9	2-2007781-2
	B	4.5	2-2007781-1
	A	5.5	1-2007781-6
	A	4.9	1-2007781-5
	A	4.5	1-2007781-4
	A	5.5	1-2007781-3
	A	4.9	1-2007781-2
	A	4.5	1-2007781-1
	-	5.5	2007781-6
	-	4.9	2007781-5
	-	4.5	2007781-4
	-	5.5	2007781-3
	-	4.9	2007781-2
	-	4.5	2007781-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2007781-2](#)