



D

C

B

A

D

C

B

A

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
-	-	SEE SHEET 1	-	-

	X-2103124-1 (KEY A)	X-2103124-2 (KEY B)	X-2103124-4 (KEY D)	X-2103124-5 (KEY E)	X-2103124-6 (KEY F)	X-2103124-7 (KEY G)
FRONT VIEW	<p>(7.20) (7.20)</p> <p>X •PA66-GF33•</p>	<p>(7.20) (9.20)</p> <p>X •PA66-GF33•</p>	<p>(9.20) (9.20)</p> <p>X •PA66-GF33•</p>	<p>(8.20)</p> <p>X •PA66-GF33•</p>	<p>(8.20)</p> <p>X •PA66-GF33•</p>	<p>(8.20) (9.20) (3.20)</p> <p>X •PA66-GF33•</p>
SIDE VIEW	<p>(15.55)</p>	<p>(15.55)</p>	<p>(15.55)</p>	<p>(15.55)</p>	<p>(15.55)</p>	<p>(15.55)</p>
REAR VIEW	<p>(0.00)</p>	<p>(5.50)</p>	<p>(8.25) (15.55)</p>	<p>(2.75) (15.55)</p>	<p>(2.75) (15.55)</p>	<p>(5.50) (15.55)</p>
INTERFACE VIEW - MOUNTING SIDE	<p>0.00 15.550</p> <p>KEY A MOUNTING INTERFACE</p>	<p>5.50 15.550</p> <p>KEY B MOUNTING INTERFACE</p>	<p>8.25 15.550</p> <p>KEY D MOUNTING INTERFACE</p>	<p>2.75 15.550</p> <p>KEY E MOUNTING INTERFACE</p>	<p>2.75 15.550</p> <p>KEY F MOUNTING INTERFACE</p>	<p>5.50 15.550</p> <p>KEY G MOUNTING INTERFACE</p>

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
T. DEWILTE

CHK
T. DEWILTE

APVD
T. DEWILTE

30SEP2010

30SEP2010

15APR2011

DIMENSIONS:

mm

0 PLC ±0.50

1 PLC ±0.50

2 PLC ±0.15

3 PLC ±0.05

4 PLC ±

ANGLES ±3

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC

APPLICATION SPEC

408-10441

WEIGHT 22.7 g

CUSTOMER DRAWING

DWN
T. DEWILTE

CHK
T. DEWILTE

APVD
T. DEWILTE

30SEP2010

30SEP2010

15APR2011

NAME

HVA280 2P HEADER ASSY
W/HVIL - PLASTIC 1 PIECE
CHART DRAWING

SIZE

A1

CAGE CODE

00779

DRAWING NO

2103124

RESTRICTED TO

-

TE Connectivity

SCALE 2:1

SHEET 2 OF 2

REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2103124-7](#)