







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IR	—						
			P2	9-216444-9 IS MADE FINISHED PRODUCT	13SEP2011	PS	RRP

NOTES:

1. TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,15$.
- MODULAR JACK P.N. 216444-1, 216444-2, 3-216444-1, 4-216444-1 ARE DELIVERED WITH PLASTIC SOLDER STOP INSTALLED, TO PREVENT SOLDER ENTERING THE JACK. REMOVE SOLDER STOP AFTER SOLDERING.
3. FOR PERFORMANCE REQUIREMENTS SEE TE PRODUCT SPECIFICATION 108-19064.
4. FOR APPLICATION REQUIREMENTS SEE TE APPLICATION SPECIFICATION 114-19019.
- FOR PACKAGING SEE SHEET 2.
- PREFERRED DIRECTION FOR STAMPING OF HOLE TO OBTAIN A BROKEN EDGE AT JACK ENTRY SIDE.
- TRUE POSITIONING OF THE SOLDER TINES MAY BE AFFECTED BY BULK PACKAGING. THE SOLDER STOP COULD BE LOOSENED DURING TRANSPORT.
- MODULAR JACK PN 9-216444-9 IS DELIVERED WITHOUT SOLDER STOP SO CUSTOMER HAS TO VERIFY THIS PART BEFORE CONSIDERING FOR MASS PRODUCTION.



<div></div>	BULK PACKED 800PCS IN A BOX	4 POS. / 4 CONTACTS WITHOUT SOLDER STOP	CONTACTS: 1,25µm MIN. GOLD OVER 1,25µm MIN. NICKEL IN CONTACT AREA. 1,25µm MIN. TIN-LEAD OVER 1,25µm MIN. NICKEL ON SOLDER TINES.	HOUSING: 20% G.F. NYLON COLOR: BLACK UL 94-HB CONTACTS: PHOS. BRONZE	9-216444-9
OBSOLETE <div></div>	800pcs PER 60cm DIA REEL	4 POS. / 4 CONTACTS WITH SOLDER STOP PACKAGED 800 pcs. ON 60cm DIA REEL		HOUSING: 25% G.F. NYLON COLOR: BLACK UL 94V-0 CONTACTS: PHOS. BRONZE	216444-2
OBSOLETE <div></div>	BULK PACKAGED 500pcs. IN A BOX	4 POS. / 4 CONTACTS WITH SOLDER STOP BULK PACKAGED 500 pcs/BOX		HOUSING: 20% G.F. NYLON COLOR: BLACK UL 94-HB CONTACTS: PHOS. BRONZE	4-216444-1
<div></div>	BULK PACKAGED 1000pcs. IN A BOX	4 POS. / 4 CONTACTS WITH SOLDER STOP BULK PACKAGED 1000 pcs/BOX			3-216444-1
<div></div>	800pcs PER 60cm DIA REEL	4 POS. / 4 CONTACTS WITH SOLDER STOP FOR PACKAGING SEE SHEET 2			216444-1
PACKAGING		REMARKS	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.V.EIJK	17DEC96	<div><div>TE</div>TE Connectivity</div>		
DIMENSIONS: mm		CHK W. BRUMMANS	—			
<div><div></div></div>		APVD R. SMEETS	—	NAME MODULAR JACK, 4 POS. BOTTOM ENTRY VERSION FOR PRINTED CIRCUIT BOARD MOUNTING		
		PRODUCT SPEC	—			
MATERIAL		APPLICATION SPEC	—	SIZE A2	CAGE CODE 00779	DRAWING NO C-216444
FINISH		WEIGHT	—	SCALE NTS	SHEET 1 of 2	REV P2
CUSTOMER DRAWING						

4


3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT	BY	ALL RIGHTS RESERVED.	

LOC		DIST		REVISIONS			
IR		—		P	LTR	DESCRIPTION	DATE
							DWN
							APVD
				—		SEE SHEET 1	—
							—



SEE DETAIL-A

REEL-OFF DIRECTION

600

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17DEC96	TE Connectivity			
		CHK	E.V.EIJK				
		APVD	W. BRUMMANS	NAME			
		PRODUCT SPEC	R. SMEETS				
		APPLICATION SPEC	—	4 POS. BOTTOM ENTRY MODULAR JACK PACKAGING			
		WEIGHT	—				
		CUSTOMER DRAWING	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A2	00779	C=216444	—
				SCALE	NTS	SHEET	REV
						2 of 2	P2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-216444-9](#)