




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		A	RELEASE	31DEC2015	JY	SH
			A1	REVISED PER ECO-19-016043	21OCT2019	SH	SH





2-2170769-2 AS SHOWN
SCALE 2:1



VIEW V-V
SCALE 2:1

- COMPONENTS
CAGE ASSEMBLY: NICKEL-SILVER ALLOY
HEAT SINK: ALUMINUM/BLACK ANODIZE
HEAT SINK CLIP: STAINLESS STEEL
EMI SPRING: COPPER ALLOY/NICKEL PLATE
LIGHT PIPE: CLEAR POLYCARBONATE
ORGANIZER: POLYESTER
- REFERENCE APPLICATION SPECIFICATION 114-32023
FOR RECOMMENDED DRILL HOLE DIAMETER AND
PLATING THICKNESS
- DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
- DIMENSION APPLIES WITH MODULE INSERTED IN CAGE
- HEAT SINKS, HEAT SINK CLIPS AND LIGHT PIPES
ARE SHIPPED ASSEMBLED ON CAGE
- MINIMUM PC BOARD THICKNESS:
SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 3.00 MIN

- DATUM **-A-** IS TOP SURFACE OF THE HOST BOARD.
- THESE HOLES ARE OPTIONAL WHEN THE REAR PINS ARE REMOVED.
- MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.
- DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.
- NOTED DIMENSIONS ONLY APPLY TO CAGE ASSEMBLY WITH LIGHT PIPE.




DETAIL C
SCALE 4:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 23APR2014	TE Connectivity			
		CHK JASON YANG 23APR2014				
		APVD SEAN HAN 31DEC2015	NAME RECEPTACLE CAGE ASSEMBLY WITH HEAT SINKS AND LIGHT PIPES, THRU BEZEL, 1X3, QSFP28			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-19428	SIZE A200779	CAGE CODE C-2170769	RESTRICTED TO -
		0 PLC ± 1 PLC ±0.25 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± FINISH	APPLICATION SPEC 114-32023	DRAWING NO C-2170769	SCALE 3:1	SHEET 1 OF 9
MATERIAL SEE NOTES		WEIGHT -	CUSTOMER DRAWING			
		SEE NOTES	REV A1			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-


HEAT SINK OPTION



SCALE 1:1




SCALE 1:1




SCALE 1:1


LIGHT PIPE OPTION



SCALE 1:1




SCALE 1:1




SCALE 1:1


OF REAR PIN OPTION



1 REAR PIN
SCALE 2:1



0 REAR PIN
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 23APR2014	 TE Connectivity			
DIMENSIONS: mm		CHK JASON YANG 23APR2014				
		APVD SEAN HAN 31DEC2015	NAME RECEPTACLE CAGE ASSEMBLY WITH HEAT SINKS AND LIGHT PIPES, THRU BEZEL, 1X3, QSFP28			
		PRODUCT SPEC 108-19428	SIZE A200779			
MATERIAL SEE NOTES material_2		APPLICATION SPEC 114-32023	DRAWING NO C-2170769			
FINISH SEE NOTES finish_spec_2		WEIGHT -	RESTRICTED TO -			
CUSTOMER DRAWING		SCALE 3:1	SHEET 1	OF 9	REV A1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0	23.0	QUAD	NETWORKING	4-2170769-6
0	16.0	QUAD	SAN	4-2170769-5
0	13.7	QUAD	PCI	4-2170769-4
1	23.0	QUAD	NETWORKING	4-2170769-3
1	16.0	QUAD	SAN	4-2170769-2
1	13.7	QUAD	PCI	4-2170769-1
0	23.0	DUAL	NETWORKING	2-2170769-6
0	16.0	DUAL	SAN	2-2170769-5
0	13.7	DUAL	PCI	2-2170769-4
1	23.0	DUAL	NETWORKING	2-2170769-3
1	16.0	DUAL	SAN	2-2170769-2
1	13.7	DUAL	PCI	2-2170769-1
0	16.0	SINGLE	W/O HS	2170769-7
0	23.0	SINGLE	NETWORKING	2170769-6
0	16.0	SINGLE	SAN	2170769-5
0	13.7	SINGLE	PCI	2170769-4
1	23.0	SINGLE	NETWORKING	2170769-3
1	16.0	SINGLE	SAN	2170769-2
1	13.7	SINGLE	PCI	2170769-1
# OF REAR PIN	DIM A	LIGHT PIPE OPTION	APPLICATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.25

2 PLC ±0.2

3 PLC ±-

4 PLC ±-

ANGLES ±-

MATERIAL

SEE NOTES

material_2

DWN

BING LIU

23APR2014

CHK

JASON YANG

23APR2014

APVD

SEAN HAN

31DEC2015

PRODUCT SPEC

108-19428

APPLICATION SPEC

114-32023

WEIGHT

-

NAME

RECEPTACLE CAGE ASSEMBLY WITH HEAT SINKS AND LIGHT PIPES, THRU BEZEL, 1X3, QSFP28

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

©-2170769

-

CUSTOMER DRAWING

SCALE

3:1

SHEET

1

OF

9

REV


A1

1471-9 (3/11)


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

D



SINGLE SIDE MOUNTING
SCALE 2:1



SINGLE SIDE MOUNTING
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.25
2 PLC	±0.2
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	

APVD

23APR2014

23APR2014

31DEC2015

PRODUCT SPEC

108-19428

APPLICATION SPEC

114-32023

WEIGHT

-

CUSTOMER DRAWING

NAME

RECEPTACLE CAGE ASSEMBLY WITH HEAT SINKS AND LIGHT PIPES, THRU BEZEL, 1X3, QSFP28

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2170769

-

SCALE

3:1

SHEET

1


OF


9


REV


A1


TE Connectivity











Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2170769-3](#)